

500 WATT TVS ARRAY



DESCRIPTION

The PAM10ST23xxC Series are transient voltage suppressor (TVS) arrays, designed for automotive applications that provide protection against ESD, tertiary lightning and switching transients. These devices offer low clamping voltage for the protection of sensitive interfaces.

The PAM10ST23xxC Series has a peak pulse power of 500 Watts for an 8/20 μ s waveshape and is available in a bidirectional configuration. This device meets the IEC 61000-4-2, 61000-4-4 and IEC 61000-4-5 requirements.

FEATURES

- **AEC-Q101 Qualified**
- Compatible with IEC 61000-4-2 (ESD): Air $\pm 30\text{kV}$, Contact $\pm 30\text{kV}$
- Compatible with IEC 61000-4-4 (EFT): 40A, 5/50ns
- Compatible with IEC 61000-4-5 (Surge): 24A, 8/20 μ s - Level 2(Line-Ground) & Level 3 (Line-Line)
- 500 Watts Peak Pulse Power per Line($t_p = 8/20\mu\text{s}$)
- Low Clamping Voltage
- Bidirectional Configuration
- Available in Multiple Voltages
- RoHS Compliant
- REACH Compliant


MECHANICAL CHARACTERISTICS

- Molded JEDEC SOT-23 Package
- Approximate Weight: 8 milligrams
- Lead-Free Pure-Tin Plating (Annealed)
- Solder Reflow Temperature:
Pure-Tin - Sn, 100: 260-270°C
- Flammability Rating UL 94V-0
- 8mm Tape and Reel per EIA Standard 481

APPLICATIONS

- Automotive Application

PIN CONFIGURATION






TYPICAL DEVICE CHARACTERISTICS


MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	500	Watts
Operating Temperature	T_L	-55 to 150	°C
Storage Temperature	T_{STG}	-55 to 150	°C

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE V_{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$ VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) @ $I_p = 1A$ V_c VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) @ 8/20μs V_c @ I_{PP}	MAXIMUM LEAKAGE CURRENT @ V_{WM} I_d μA	TYPICAL CAPACITANCE @ 0V, 1MHz C pF
PAM10ST2303C	03C	3.3	4.0	7.0	10.9V @ 43.0A	125	300
PAM10ST2305C	05C	5.0	6.0	9.8	13.5V @ 42.0A	20	210
PAM10ST2308C	08C	8.0	8.5	13.4	16.9V @ 34.0A	10	150
PAM10ST2312C	12C	12.0	13.3	19.0	25.9V @ 21.0A	2	90
PAM10ST2315C	15C	15.0	16.7	24.0	30.0V @ 17.0A	1	60
PAM10ST2324C	24C	24.0	26.7	43.0	49.0V @ 12.0A	1	63
PAM10ST2336C	36C	36.0	40.0	51.0	76.8V @ 9.0A	1	60

TYPICAL DEVICE CHARACTERISTICS

FIGURE 1
 PEAK PULSE POWER VS PULSE TIME

FIGURE 2
 PULSE WAVE FORM

FIGURE 3
 POWER DERATING CURVE


SPICE MODEL

FIGURE 1
 SPICE MODEL FOR

 ABD - Avalanche Breakdown Diode (TVS)
 Lg - Lead Inductance
TABLE 1 - SPICE PARAMETERS

PARAMETER	UNIT	ABD(TVS)
BV	V	See Table 2
IBV	μ A	1
C_{jo}	pF	See Table 2
I_s	A	See Table 2
Vj	V	0.6
M	-	0.33
N	-	1
R_s	Ohms	See Table 2
TT	s	1E-8
EG	eV	1.11

TABLE 2 - ABD SPECIFIC SPICE PARAMETERS


PART NUMBER	B_v (VOLTS)	C_{jo} (pF)	I_s (AMPS)	R_s (OHMS)
PAM10ST2303C	4.5	219	1E-13	0.28
PAM10ST2308C	8.5	73	1E-13	0.28
PAM10ST2315C	16.7	51	1E-13	0.52
PAM10ST2324C	26.7	30	1E-13	0.28
PAM10ST2336C	40.0	20	1E-13	0.28

SOT-23 PACKAGE INFORMATION

DIM	OUTLINE DIMENSIONS			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	2.80	3.04	0.110	0.120
B	1.20	1.40	0.047	0.055
C	0.89	1.11	0.035	0.044
D	0.37	0.50	0.015	0.020
G	1.78	2.04	0.070	0.081
H	0.013	0.100	0.001	0.004
J	0.085	0.177	0.003	0.007
K	0.45	0.60	0.018	0.024
L	0.89	1.02	0.035	0.040
S	2.10	2.50	0.083	0.098
V	0.45	0.60	0.018	0.024

NOTES


1. Controlling dimension: inches.
2. Dimensioning and tolerances per ANSI Y14.5M, 1985.
3. Pin 3 is the cathode (Unidirectional Only)
4. Dimensions are exclusive of mold flash and metal burrs.




DIM	PAD LAYOUT DIMENSIONS			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	0.71	0.97	0.028	0.038
B	1.88	2.13	0.074	0.084
C	0.71	0.97	0.028	0.038
D	0.81	1.07	0.032	0.042

NOTES

1. Controlling dimension: inches.



TAPE AND REEL



SPECIFICATIONS

REEL DIA.	TAPE WIDTH	A0	B0	K0	D	E	F	W	P0	P2	P	tmax
178mm (7")	8mm	3.15 ± 0.10	2.77 ± 0.10	1.30 ± 0.10	1.55 ± 0.10	1.75 ± 0.10	3.50 ± 0.05	8.00 ± 0.30	4.00 ± 0.10	2.00 ± 0.05	4.00 ± 0.10	0.228

NOTES

1. Dimensions are in millimeters.
2. Surface mount product is taped and reeled in accordance with EIA-481.
3. Marking on Part - marking code (see page 2).

ORDERING INFORMATION

BASE PART NUMBER (xx = VOLTAGE)	LEADFREE SUFFIX	TAPE SUFFIX	QTY/REEL	REEL SIZE	TUBE QTY
PAM10ST23xxC	n/a	-T7	3000	7"	n/a
PAM10ST23xxC	n/a	-T13	10,000	13"	n/a

This device is only available in a Lead-Free configuration.

COMPANY INFORMATION

COMPANY PROFILE

In business more than 25 years, ProTek Devices™ is a privately held semiconductor company. The company offers a product line of overvoltage protection and overcurrent protection components. These include transient voltage suppressor array (TVS arrays) avalanche breakdown diode, steering diode TVS array and electronics SMD chip fuses. These components deliver circuit protection in electronic systems from numerous overvoltage and overcurrent events. They include lightning; electrostatic discharge (ESD); nuclear electromagnetic pulses (NEMP); inductive switching; and electromagnetic interference (EMI) / radio frequency interference (RFI). ProTek Devices also offers LED wafer die for ESD protection and related high frequency products. ProTek Devices is an ISO 9001 certified company.

CONTACT US

Corporate Headquarters

2929 South Fair Lane
 Tempe, Arizona 85282
 USA

By Telephone

General: 602-431-8101
 Sales: & Marketing: 602-414-5109
 Customer Service: 602-414-5114
 Product Technical Support: 602-414-5107

By Fax

General: 602-431-2288

By E-mail:

Asia Sales: asiasales@protekdevices.com
 Europe Sales: europesales@protekdevices.com
 U.S. Sales: ussales@protekdevices.com
 Distributor Sales: distysales@protekdevices.com
 Customer Service: service@protekdevices.com
 Technical Support: support@protekdevices.com

ProTek Devices (Asia Pacific) Pte. Ltd.

8 Ubi Road 2, #06-19
 Zervex
 Singapore - 408538
 Tel: +65-67488312
 Fax: +65-67488313

Web

www.protekdevices.com

COPYRIGHT © ProTek Devices 2011 - This literature is subject to all applicable copyright laws and is not for resale in any manner.

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice.

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance. ProTek assumes no responsibility with respect to the selection or specifications of such products. ProTek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ProTek assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability without limitation special, consequential or incidental damages.

LIFE SUPPORT POLICY: ProTek Devices products are not authorized for use in life support systems without written consent from the factory.