


5 4 3 2 1


Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802

No. 1 contact

12,5 max.



screw lock thread



Printed board layout
component side

$$4 \times 2,74 = 10,96$$

$$3 \times 2,74 = 8,22$$


$$2,74$$

No.1 contact

$$\phi 3,1 \pm 0,1 \quad \phi 0,1$$


max. 3,2
6,2

$$0,6$$




$$25 \pm 0,1$$

$$31,2 \text{ max.}$$



Connector retention and insertion forces on the PCB = 25 / 80 newtons

A	09 65 161 6733	M3	2							 All Dim. in mm Orig. Size DIN A 4	D-Sub, 9 poles, male, straight with solder pins 3.7, screw lock and grounding board lock.	Maßstab/ Scale 1,5:1
	09 65 161 7733	M3	3									
	09 65 161 5733	M3	0.76 µm Au									
	09 65 161 6713	4-40 UNC	2							 HARTING EURL F-95972 Paris	TB 09 65 161 X7X3	Blatt/ Page 1
	09 65 161 7713	4-40 UNC	3	29723	05-MAR-02	CV						
	09 65 161 5713	4-40 UNC	0.76 µm Au	29746	07-FEB-02	JB						
	Part number	Screw lock thread	Performance level	Mod.	Dat.	Name					Sub.	