


## Double Pole, Electrically Held, 1 Amp and Less (Continued)

MST

MST

**Sensitive T0-5  
Diode Suppressed/  
Transistor Driven  
High Performance Relay  
Qualified to MIL-R-28776/3**



Terminal View

### Product Facts

- Transistor driver & suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pads
- Excellent RF switching

### Electrical Characteristics

**Contact Arrangement** —  
2 Form C (DPDT)

**Contact Material** —  
Stationary —  
Gold/platinum/palladium/silver alloy  
(gold plated)  
Moveable —  
Gold/platinum/palladium/silver alloy  
(gold plated)

**Contact Resistance** —  
Before Life — 100 milliohms max.  
(measured @ 10 mA @ 6 Vdc)  
After Life — 200 milliohms max.  
(measured @ 1 A @ 28 Vdc)

**Mechanical Life Expectancy** —  
1 million operations

**Coil Voltage** — 5 to 48 Vdc

**Coil Power** — 565 mW max. @ 25°C


**Duty Cycle** — Continuous

**Pick-up Voltage** — Approximately  
50% of nominal coil voltage

**Pick-up Sensitivity** —  
60 mW max. @ 25°C

### Contact Ratings

| Contact Load                     | Type                          | Operations Min. |
|----------------------------------|-------------------------------|-----------------|
| 1.0 A @ 28 Vdc                   | Resistive                     | 100,000         |
| 250 mA @ 115 Vac, 60 Hz & 400 Hz | Resistive (case not grounded) | 100,000         |
| 100 mA @ 115 Vac, 60 Hz & 400 Hz | Resistive                     | 100,000         |
| 0.2 A @ 28 Vdc                   | Inductive (0.32 Henry)        | 100,000         |
| 0.1 A @ 28 Vdc                   | Lamp                          | 100,000         |
| 30 µA @ 50 mVdc                  | Low Level                     | 1,000,000       |
| 0.1 A @ 28 Vdc                   | Intermediate Current          | 50,000          |



## Double Pole, Electrically Held, 1 Amp and Less (Continued)

### MST (Continued)

#### Operating Characteristics

##### Timing —

Operate Time — 4.0 ms max.

Release Time — 7.5 ms max.

**Contact Bounce** — 1.5 ms max

##### Dielectric Withstanding Voltage —

Between Open Contacts —

500 Vrms 60 Hz

Between Adjacent Contacts —

500 Vrms 60 Hz

Between Contacts & Coil —

500 Vrms 60 Hz

##### Insulation Resistance —

10,000 megohms min. @ 500 Vdc

1,000 megohms @ 500 Vdc

(coil to case @ +125°C)

#### Environmental Characteristics

##### Temperature Range —

-65°C to +125°C

##### Weight —

0.12 oz. (3.40 grms)

0.13 oz. (3.45 grms) with spreader pad attached

##### Vibration Resistance —

30 G's, 10 to 3,000 Hz

##### Shock Resistance —

75 G's, 6 ±1 ms max.

##### QPL Approval —

MIL-R-28776/3 (JMST)

#### Semiconductor Characteristics

##### Diode —

100 Vdc peak inverse voltage (PIV)

1.0 Vdc max. transient voltage

##### Transistor —


0.3 Vdc min. base turn off voltage;

6.0 Vdc min. emitter-base breakdown

voltage (BV<sub>EB0</sub>) @ 25°C;

80.0 Vdc min. collector-base breakdown

voltage (BV<sub>CB0</sub>) @ 25°C & I<sub>C</sub>=100 µA



Spreader & Mounting Pads

### Coil Data

| Nom. Coil Voltage (Vdc) | Coil Resistance in Ohms ±10% @ 25°C (Note 1) | Coil Circuit Current mA (Max.) (Note 1 & 2) | Coil Circuit Current mA (Min.) (Note 1 & 2) | Pickup Voltage Vdc (Max.) @ 25°C (Note 2) | Base Turn On Current mA (Max.) @ 25°C | Pickup Voltage Vdc (Max.) @ 125°C (Note 2) | Base Turn On Current mA (Max.) @ 125°C | Drop-Out Voltage Vdc (Min.) @ 25°C (Note 2) | Drop-Out Voltage Vdc (Min.) @ -65°C (Note 2) | Nom. Coil Power (mW) @ 25°C | Max. Coil Voltage | Coil Desig. |
|-------------------------|----------------------------------------------|---------------------------------------------|---------------------------------------------|-------------------------------------------|---------------------------------------|--------------------------------------------|----------------------------------------|---------------------------------------------|----------------------------------------------|-----------------------------|-------------------|-------------|
| MST                     |                                              |                                             |                                             |                                           |                                       |                                            |                                        |                                             |                                              |                             |                   |             |
| 5.0                     | 100                                          | 59.3                                        | 43.5                                        | 2.8                                       | 0.37                                  | 3.6                                        | 1.50                                   | 0.22                                        | 0.14                                         | 250                         | 7.0               | 5           |
| 6.0                     | 200                                          | 35.4                                        | 26.4                                        | 3.8                                       | 0.25                                  | 4.8                                        | 1.00                                   | 0.28                                        | 0.18                                         | 180                         | 10.0              | 6           |
| 9.0                     | 400                                          | 25.8                                        | 19.7                                        | 5.2                                       | 0.18                                  | 7.8                                        | 0.75                                   | 0.54                                        | 0.35                                         | 203                         | 15.0              | 9           |
| 12.0                    | 850                                          | 16.7                                        | 12.2                                        | 7.4                                       | 0.12                                  | 11.0                                       | 0.47                                   | 0.63                                        | 0.41                                         | 169                         | 20.0              | 12          |
| 18.0                    | 1,600                                        | 13.1                                        | 9.7                                         | 10.0                                      | 0.09                                  | 14.5                                       | 0.38                                   | 0.91                                        | 0.59                                         | 203                         | 30.0              | 18          |
| 26.5                    | 3,300                                        | 9.5                                         | 6.9                                         | 14.2                                      | 0.06                                  | 19.0                                       | 0.24                                   | 1.37                                        | 0.89                                         | 213                         | 40.0              | 26          |
| 36.0                    | 6,500                                        | 6.4                                         | 4.8                                         | 20.0                                      | 0.034                                 | 27.0                                       | 0.17                                   | 1.80                                        | 1.25                                         | 199                         | 57.0              | 36          |
| 48.0                    | 11,000                                       | 5.1                                         | 3.7                                         | 25.8                                      | 0.026                                 | 36.0                                       | 0.13                                   | 2.40                                        | 1.60                                         | 209                         | 75.0              | 48          |

**Notes:** 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.  
2. Set base current at 3 mA to 15 mA during measurements.

### Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the relay characteristics in the order in which the codes are listed.

#### Specifying a Part Number Example:

| Type | Terminal | Diodes | Ground Pins | Coils | Spreader/Mounting Pads |
|------|----------|--------|-------------|-------|------------------------|
| MS   | C        | T      | G           | -26   | S                      |

\* The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.