


© 2023 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECN-23-203008	15MAR2023	IT	SZ







NOTES:

UNLESS OTHERWISE SPECIFIED

1. MATERIAL: 6063 ALUMIMUM.
2. FINISH: ANODIZATION, NATURAL.
3. 0,2mm MAX BURR.
4. VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
5. MAXIMUM PIN LEAN OF 8° IN ANY DIRECTION.
6. RoHS COMPLIANT AND CERTIFIED.
7. FINISH: HARD ANODIC COATING PER MIL-A-8625 TYPE III, 40.64 MICROMETERS MINIMUM THICK.

7	1829905-4
2	1829905-2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±.2
2 PLC ±.10
3 PLC ±.08
4 PLC ±0.0001
ANGLES ±5

MATERIAL 1 material_2

FINISH 2 finish_spec_2

DWN E.TAO 6-26-06
CHK V.KHEIL 7-13-06
APVD - -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME HEAT SINK SFP DWDM 13.5mm TALL

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1829905	-

CUSTOMER DRAWING | SCALE 4.000 | SHEET 1 OF 1 | REV C3

printed on 16 Mar 2023 08:35 (China Standard Time) from FG086105

Downloaded from Arrow.com.