




The Si2167 programmable Transport Stream interface provides a flexible range of output modes and is fully compatible with all MPEG decoders or conditional access modules to support any customer application.

- DVB-T (ETSI EN 300 744)
 - COFDM demodulator & FEC decoder
 - NorDig Unified 2.1, D-Book 6.1 compliant
 - Supports all C.R., G.I., LP, and HP streams
- DVB-C (ETSI EN 300 429) / ITU J.83 Annex A/C
 - QAM demodulator & FEC decoder
 - 1 to 7.2 MSymbol/s
 - C-Book compliant
- DVB-S2 (ETSI EN 302 307 & TR102-376)
 - QPSK/8PSK demodulator and FEC decoder
 - Broadcast profile: CCM, 64800 bits frame, single TS
 - 1 to 45 MSymbol/s (optimized for 2 to 32 MSymbol/s)
 - DIRECTV™ AMC compatible
- DVB-S (ETSI EN 300 421)
 - QPSK demodulator & FEC decoder
 - 1 to 45 MSymbol/s
- DIRECTV™ DSS compliant
- DiSEqC™ 2.0 interface
- I²C serial bus interfaces (Master & Host)
- Three ADCs with independent IF and ZIF (differential) inputs for terrestrial/cable and satellite
- GPIOs and multi-purpose ports for independent AGCs (up to 4) to control satellite and T/C tuners
- Embedded ADC for RSSI monitoring
- Flexible TS interface with serial or parallel single output
- Fast lock times for all media
- Only two power supplies: 1.2 and 3.3 V
- 7x7 mm, QFN-48 pin package, Pb-free/RoHS compliant

- Full-NIM
- iDTV (integrated Digital TV)
- Digital terrestrial, cable, and satellite STB
- PC-TV accessories
- PVR, DVD, and Blue Ray disc recorders




Selected Electrical Specifications

(T_A = -20 to 75 °C)

Parameter	Test Condition	Min	Typ	Max	Unit
General					
Input clock reference		4	—	30	MHz
Supported XTAL frequency		16	—	30	MHz
Total power consumption	DVB-T	—	190	—	mW
	DVB-S ¹	—	270	—	mW
	DVB-S2 ²	—	860	—	mW
Thermal resistance	2 layer PCB	—	32	—	°C/W
	4 layer PCB	—	23	—	°C/W
Input ADC Sampling Clock					
Satellite DVB-S	45 MBaud	91	94	101	MHz
Satellite DVB-S2	32 MBaud	65	70	101	MHz
DVB-T/C	36 MHz standard IF/low-IF	—	56	65	MHz
Power Supplies					
V _{DD_VCORE}		1.10	1.20	1.30	V
V _{DD_VANA}		3.00	3.30	3.60	V
V _{DD_VIO}		2.25	2.50/3.30	3.60	V
Notes:					
1. Most power intensive demodulation: 45 MBaud, CR=7/8, adc_clock= 96 MHz, parallel TS (at QEF: BER = 2. 10 ⁻⁴).					
2. Most power intensive demodulation: 30 MBaud, 3/5 Code Rate, 8PSK, pilots On, C/N at picture failure (PER = 10 ⁻⁴).					

Pin Assignments



Selection Guide

Part #	Description
Si2167-A10-FM	Multimedia Digital TV Demodulator for DVB-T/C/S/S2, 7x7 mm QFN-48.