**Part Number :** 1200730645
**Product Description :** M12 Signal, C-Coded, Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 18 AWG, Yellow PVC Cable, Yellow Overmold, 10.67m (35.0') Length
**Series Number :** 120073
**Status :** Active
**Product Category :** Circular Industrial Cordsets
**Engineering Part Number :** 774030A03F350




## Documents and Resources

### Drawings

1200730645_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 120073 |
| Description | M12 Signal, C-Coded, Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 18 AWG, Yellow PVC Cable, Yellow Overmold, 10.67m (35.0') Length |
| IP Rating | IP67 |
| Product Name | M12 Signal,Micro-Change (M12) |
| Type | Double Ended |
| UPC | 78172546950 |

### Agency

| | |
|---|---|
| CSA | LR6837 |
| UL | E152210 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 250V AC/DC |

### Physical

| | |
|---|---|
| Cable Diameter | 6.10mm (.240") |
| Cable Length | 10.67m (35.0') |
| Color - Cable Jacket | Yellow |
| Connector End A | M12 Signal |
| Connector End B | M12 Signal |

Downloaded from Arrow.com.

| | |
|---|---|
| Coupling Style | Threaded |
| Gender | Female-Male |
| Keyway | C-Coded |
| LED Indicator | No |
| Material - Cable Jacket | PVC |
| Material - Connector Body | TPC |
| Material - Contact | Copper Alloy |
| Material - Coupling Nut | Black Epoxy Coated Zinc |
| Material - O-Ring | Nitrile Rubber |
| Material - Plating Mating | Gold |
| Net Weight | 55.550/g |
| Orientation | Straight to Straight |
| Poles | 4 |
| Temperature Range - Operating | -25° to +105°C |
| Wire/Cable Type | UL 2661 |
| Wire Size (AWG) | 18 |



Downloaded from Arrow.com.