



Part Number : 2029881242

Series Number : 202988

Product Category : Crimp Terminals

Product Description : Mini-Fit TPA2/Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag

Status : Active


Packaging Alternative : 2029881241 (Reel)

Documents & Resources

- Drawings**
- [Drawing 2029881242_sd.pdf](#)
 - [Packaging Design Drawing 2029880003-000.pdf](#)
- Specifications**
- [Application Specification AS-172718-0000-001.pdf](#)
 - [Application Specification 2131370000-AS-000.pdf](#)
 - [Product Specification 2029880001-PS-000.pdf](#)
 - [Product Specification 2029880002-PS-000.pdf](#)
 - [Test Summary 2029880001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	202988
Description	Mini-Fit TPA2/Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag
Application	Power, Wire-to-Wire, Wire-to-Board
Comments	See product specification for current derating information.
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma,Mini-Fit TPA2
UPC	191128369596

Electrical

Current - Maximum per Contact	13.5A
Voltage - Maximum	600V AC/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.211/g
Packaging Type	Bag
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	1.98-2.55mm
Wire Size (AWG)	16
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Receptacle Housings	<u>172708</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 16 AWG, Large and Small Insulation Grips	<u>2002181700</u>

This document was generated on Jul 29, 2024