Part Number : 1200688282
Product Description : Micro-Change (M12) In-Line Splitter, 4-Pole Male to 2 x 4-Pole Female, 22 AWG, 0.80m Length
Series Number : 120068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : 884A30B30M003



Documents and Resources

Drawings

1200688282_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Micro-Change (M12) In-Line Splitter, 4-Pole Male to 2 x 4-Pole Female, 22 AWG, 0.80m Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Splitter - In-line
UPC	193264044610

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Color - Cable Jacket	Black
Drop Connector	N/A
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	0.30m
Leg 2 Length	0.50m

Downloaded from Arrow.com.

Material - Cable Jacket	TPU
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Net Weight	63.200/g
Poles	4
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-20°C to +80°C

Downloaded from Arrow.com.