

Microchip**Filter specification****TFS 480D****1/5****Measurement condition**

Ambient temperature T_A :	23	°C
Input power level:	10	dBm
Terminating impedance: *		
Input:	700 Ω	-0.92 pF
Output:	700 Ω	-0.92 pF
External Coil:	59	nH

Characteristics

Remark:

The reference level for the relative attenuation a_{rel} of the TFS 480D is the minimum of the pass band attenuation a_{min} . The minimum of the pass band attenuation a_{min} is defined as the insertion loss a_e . The centre frequency f_c is the arithmetic mean value of the upper and lower frequencies at the 3 dB filter attenuation level relative to the insertion loss a_e . The nominal frequency f_N is fixed at 480 MHz without any tolerance. The given values for both the relative attenuation a_{rel} and the group delay ripple have to be achieved at the frequencies given below even if the centre frequency f_c is shifted due to the temperature coefficient of frequency TC_f in the operating temperature range and due to a production tolerance for the centre frequency f_c .

D a t a										typ. value		tolerance / limit				
Insertion loss (reference level)										a_e	4.4	dB	max.	6.5	dB	
Nominal frequency										f_N	-			480.0	MHz	
Centre frequency										f_C	480.0	MHz		-		
Passband										PB	-		f_N	\pm	88.0 kHz	
Bandwidth										BW						
3		dB						442	kHz							
Relative attenuation										a_{rel}						
f_N	-	100.0	MHz	...	f_N	-	91.4	MHz	57	dB	min.	45	dB			
f_N	-	91.4	MHz	...	f_N	-	16.0	MHz	43	dB	min.	31	dB			
f_N	-	16.0	MHz	...	f_N	-	2.5	MHz	54	dB	min.	45	dB			
f_N	-	2.5	MHz	...	f_N	-	1.6	MHz	50	dB	min.	37	dB			
f_N	\pm	1.2	MHz	...	f_N	\pm	1.6	MHz	43	dB	min.	32	dB			
f_N	+	1.6	MHz	...	f_N	+	2.1	MHz	47	dB	min.	35	dB			
f_N	+	2.1	MHz	...	f_N	+	3.4	MHz	45	dB	min.	37	dB			
f_N	+	3.4	MHz	...	f_N	+	6.8	MHz	53	dB	min.	42	dB			
f_N	+	6.8	MHz	...	f_N	+	100.0	MHz	62	dB	min.	51	dB			
Group delay ripple within PB										0.4	μ s	max.	2	μ s		
Operating temperature range										OTR	-	- 40 °C ... + 85°C				
Storage temperature range										-	- 55 °C ... + 125°C					
Frequency inversion temperature										30	°C	-				
Temperature coefficient of frequency										TC_f **	-0.03	ppm/K ²	-			

*) The terminating impedances depend on parasitics and q-values of matching elements and the board used, and are to be understood as reference values only. Should there be additional questions do not hesitate to ask for an application note or contact our design team.

**) $\Delta f = TC_f(T - T_0)^2 f_N$

Generated:**Checked / Approved:**

Microchip Frequency Technology GmbH



Potsdamer Straße 18

D 14 513 TELTOW / Germany

Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30


Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Filter characteristic




Construction and pin connection

(All dimensions in mm)



1	Output
2	Output
3	External Coil
4	Ground
5	Input
6	Input
7	Ground
8	Ground

Date code: Year + week
 K 2018
 L 2019
 M 2020
 ...

50 Ω Test circuit

Microchip Frequency Technology GmbH

Potsdamer Straße 18

D 14 513 TELTOW / Germany

Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Stability characteristics, reliability

After the following tests the filter shall meet the whole specification:

1. Shock: 500 g, 1 ms, half sine wave, 3 shocks each plane;
DIN IEC 60068 T2 - 27
2. Vibration: 10 Hz to 2000 Hz, 0.35 mm or 5 g respectively, 1 octave per min, 10 cycles per plane, 3 planes; DIN IEC 60068 T2 - 6
3. Change of temperature: -55 °C to 125 °C / 15 min. each / 100 cycles
DIN IEC 60068 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: three times max.;
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;
5. SAW devices are Electrostatic Discharge (ESD) sensitive devices.

This filter is RoHS compliant (2011/65/EU)

Packing

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;
tape type II, embossed carrier tape with top cover tape on the upper side;


reel of empty components at start: min. 300 mm
reel of empty components at start including leader: min. 500 mm
trailer: min. 300 mm

Tape (all dimensions in mm)

W	: 12.00 +0.3/-0.1
Po	: 4.00 ±0.1
Do	: 1.50 ±0.10
E	: 1.75 ±0.1
F	: 5.50
G(min)	: 0.75
P2	: 2.00 ±0.1
P1	: 8.00
D1(min)	: 1.50
Ao	: 5.30 ±0.1
Bo	: 5.30 ±0.1
Ct	: 9.2 ±0.1
Ko	: 2.10 ±0.1
t	: 0.30 ±0.05

Reel (all dimensions in mm)

A	: 330 or 180
W1	: 12.4 +2/-0
W2(max)	: 18.40
N(min)	: 50.00
C	: 13.0



The minimum bending radius is 45 mm.

Microchip Frequency Technology GmbH

Potsdamer Straße 18


D 14 513 TELTOW / Germany

Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Air reflow temperature conditions

Conditions	Exposure
Average ramp-up rate (30 °C to 217 °C)	less than 3 °C / second
> 100 °C	between 300 and 600 seconds
> 150 °C	between 240 and 500 seconds
> 217 °C	between 30 and 150 seconds
Peak temperature	max. 260 °C
Time within 5 °C of actual peak temperature	between 10 and 30 seconds
Cool-down rate (Peak to 50 °C)	less than 6 °C / second
Time from 30 °C to Peak temperature	no greater than 300 seconds

Chip-mount air reflow profile**Microchip Frequency Technology GmbH****Potsdamer Straße 18****D 14 513 TELTOW / Germany****Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Microchip**Filter specification****TFS 480D****5/5****History**

Version	Reason of Changes	Name	Date
1.0	- Generation of development specification.	Strehl	04.03.2008
1.1	- Generation of filter specification	Strehl	07.05.2008
2.0	- Update temperature range - Change tape and reel direction	Bonnen	07.03.2018

Microchip Frequency Technology GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.