

Representative Image

Catalog No. TY28M-2

Description: CABLE TIE 50LB 14IN RED NYLON

UPC No 786210845081

Home > Wire & Cable Management > Ty-Rap > Cable ties

High Performance Cable Tie for Indoor Applications, Red Color Nylon 6.6, Length of 361mm (14.2 Inches) for Bundle Diameter up to 102mm (4.02 Inches), Width of 4.9mm (0.19 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-2-2), Bulk Pack

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Red
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 222 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.19 in , 4.9 mm
Length	14.2 in , 361 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.12 to 4.02 in , 3 to 102 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant

ETIM Classification

ETIM	EC000046 Cable tie
Band width	0.19 inch

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Max. bundle diameter	4.02 inch
Colour	Red
Band width	4.8 mm
Length belt/tape/tie	361 mm
Length belt/tape/tie	14.2 inch
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	102 mm
Min. holding force	222 N
Operation temperature	-60-+85 °C
Operation temperature	-76-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.