


[All Categories](#) > [EMI Solutions](#) > [EMI Shielding & Gaskets](#) > [Wire Mesh & Knitted Gaskets](#) > [Ultraflex Electronit Beryllium Copper Knitted Wire Shielding](#) > [UltraFlex D with PSA Copper Knitted Wire Shielding](#) > [Ultrasoft Knit EMI Gaskets](#) > [Metallized Conductive Fabric](#) > [UltraFlex Hollow Core Round Copper Knitted Wire Shielding](#) Item # 8101-0106-40


Item # 8101-0106-40, UltraFlex Hollow Core Round Copper Knitted Wire Shielding

UltraFlex ElectroNit combines the optimum mechanical properties of beryllium copper with shielding effectiveness as much as 20 dB higher than conventional materials. It offers superb resiliency for consistent, point -to-point contact requiring the lowest compression forces among all other shielding materials and configurations. A wide range of platings, sizes, configurations, and excellent flexibility create optimum design latitude.

? Other platings available upon request



[larger image](#)



[larger image](#)

Specifications

Groove Dimensions W	0.187 inches
Groove Dimensions W	4.8 mm
Groove Dimensions H	0.24 inches
Groove Dimensions H	6.1 mm
Diameter	0.25 inches
Diameter	6.4 mm
Groove Dimensions W Tolerance	+0.030 inches
Groove Dimensions W Tolerance	+0.8 mm
Groove Dimensions H Tolerance	+0.030 inches
Groove Dimensions H Tolerance	+0.8 mm
Diameter Tolerance	+0.030 inches
Diameter Tolerance	+0.8 mm
Plating Options	Cadmium Plate Nickel Plate Tin Plate Zinc Clear Chromate