


3 Amp Schottky Rectifier

1N5820, 1N5821, 1N5822



Dim.	Inches		Millimeter		Notes
	Minimum	Maximum	Minimum	Maximum	
A	.188	.260	4.78	6.50	Dia.
B	1.00	---	25.4	---	
C	.285	.375	7.24	9.52	
D	.046	.056	1.17	1.42	Dia.

PLASTIC D0201AD

Microsemi
Catalog Number

1N5820
1N5821
1N5822

Working
Peak Reverse
Voltage

20V
30V
40V

Repetitive
Peak Reverse
Voltage

20V
30V
40V

- Schottky Barrier Rectifier
- Guard ring protection
- Low forward voltage
- High reliability
- High current capability
- Reverse energy tested

Electrical Characteristics

		1N5820	1N5821	1N5822	
Average forward current	$I_F(AV)$	3A	3A	3A	$R_{\theta JL} = 18^\circ C/W, L = 3/8"$ 8.3ms, half sine, $T_J = 150^\circ C$ $I_{FM} = 1A, T_J = 25^\circ C^*$ $I_{FM} = 3A, T_J = 25^\circ C^*$ $I_{FM} = 9.4A, T_J = 25^\circ C^*$ $V_{RRM}, T_J = 25^\circ C$ $V_R = 5.0V, T_J = 25^\circ C$
Lead temperature	T_L	109°C	100°C	90°C	
Maximum surge current	I_{FSM}	150A	150A	150A	
Max peak forward voltage	V_{FM}	.36V	.37V	.38V	
Max peak forward voltage	V_{FM}	.46V	.48V	.50V	
Max peak forward voltage	V_{FM}	.65V	.67V	.70V	
Max peak reverse current	I_{RM}	1.5mA	1.5mA	1.5mA	
Typical junction capacitance	C_J	265pF	265pF	265pF	

*Pulse test: Pulse width 300 μ sec, Duty cycle 2%

Thermal and Mechanical Characteristics

Storage temperature range	T_{STG}	-55°C to 150°C
Operating junction temp range	T_J	-55°C to 150°C
Maximum thermal resistance	$L = 3/8"$ $R_{\theta JL}$	18°C/W Junction to lead
Weight		.032 ounces (1.0 grams) typical

1N5820, 1N5821, 1N5822

Figure 1
Typical Forward Characteristics




Figure 3
Typical Junction Capacitance




Figure 2
Typical Reverse Characteristics

