





Electrical data	
Operating voltage	≤ 125 VAC/VDC
Nominal current	1 A
Contact resistance (max.)	15 mΩ
Specialty functions	With shield connection

Safety and protection	
Rated Voltage	125 V
Rated impulse withstand voltage	0.8 kV
Pollution degree	2
Protection type	IP20

Connection data			
Performance level	3 / 50 mating cycles	Connection 1	
Strain relief	UNC 4-40 stud bolt	Pluggable connector	HD D-sub male connector
		Pole number 1	62
		Connection type	System
		Note (conductor cross-section)	12 AWG: THHN, THWN
		Mating direction	vertical

Connection 2	
Design	PCB terminal blocks (triple-deck)
Pole number	64
Connection type	Field
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 737 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches



Physical data		
Width		62 mm / 2.441 inches
Height		85 mm / 3.346 inches
Depth from upper-edge of DIN-rail		62 mm / 2.441 inches

Mechanical data		
Mounting type		DIN-35 rail
Housing design		Mounting carrier

Material data		
Contact material (connector)		Au over Ni
Fire load		1.151 MJ
Weight		170.8 g

Environmental requirements		
Ambient temperature (operation)		-20 ... +55 °C
Ambient temperature (storage)		-40 ... +70 °C
Relative humidity		≤ 85 % (non-condensing)

Standards and specifications		
Standards/specifications		EN 61010-2-201

Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
PU (SPU)		4 (1) pcs
Packaging type		Box
Country of origin		DE
GTIN		4017332817202
Customs tariff number		85366990990

Product Classification		
UNSPSC		39121421
eCl@ss 10.0		27-14-11-52
eCl@ss 9.0		27-14-11-52
ETIM 9.0		EC002780
ETIM 8.0		EC002780
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
CAS-No.		7439-92-1
REACH Candidate List Substance		Lead
RoHS Compliance Status		Compliant,With Exemption
RoHS Exemption		6(c)
SCIP notification number (Austria)		008238af-7e58-409b-a80f-1d465ad920f9
SCIP notification number (Belgium)		41b525f5-0928-4d5d-a4af-da18e543a037
SCIP notification number (Bulgaria)		38839f4f-a31f-407d-8738-c3eeac1a8d87
SCIP notification number (Czech Republic)		e326402f-f3fb-46ab-83ea-aca01d3ebcf3
SCIP notification number (Denmark)		49121548-7b27-48bf-a2e3-e1d6c93e469b
SCIP notification number (Finland)		ce7fd2c5-4a29-4c22-89dd-a6f575590b05
SCIP notification number (France)		f1a581ef-1f7a-4179-8006-d04fa2e77e4a



Environmental Product Compliance	
SCIP notification number (Germany)	220fb34a-b523-4db3-b4d4-22140de252f2
SCIP notification number (Hungary)	c777e863-b321-445b-9d02-4ed2af5b8186
SCIP notification number (Italy)	eacaaaa2-5393-490b-bcd7-26707cae2c1b
SCIP notification number (Netherlands)	ff6511c9-72db-475f-a6df-3efaf96e36f1
SCIP notification number (Poland)	a9a9a2e8-13f0-45d0-ae91-df17105702ad
SCIP notification number (Romania)	4daef53c-1d5b-4d7a-9a2e-ca477024ae22
SCIP notification number (Sweden)	64e4a169-dbd3-4304-a6da-e0573cfda631

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03084

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 289-710

↓

Documentation

Bid Text

289-710

19.02.2019

xml
3.58 KB

↓

289-710

09.02.2015

doc
27.00 KB

↓

Instruction Leaflet

Operation and Assembly Instructions Interface

V 1.0.0
02.04.2025

pdf
1246.19 KB

↓

CAD/CAE-Data

CAE data

EPLAN Data Portal 289-710

↓

WSCAD Universe 289-710

↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



Item No.: 709-196
Marking strips; for laser printer; translucent



Item No.: 709-177
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; translucent



Item No.: 709-178
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; white

1.1.2 Tool

1.1.2.1 Operating tool




Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

Installation Notes

Conductor termination




Conductor termination – screwdriver actuation parallel to conductor entry




Conductor termination – screwdriver actuation perpendicular to conductor entry

Installation



Snapping a module onto DIN-rail.



Removing a module from the DIN-rail.