


	1	2	3	4	5	6	7																					
A	Notes Material:SR25 Dielectric strength: 380kV/cm Heat resistance:215°C Tensile strength: 80N/mm 							A																				
B								B																				
C								C																				
D								D																				
E								E																				
F								F																				
G	RoHS compliant	<table><tr><td>Scale</td><td>1:1</td></tr><tr><td>TOLERANCE</td><td></td></tr><tr><td>X.</td><td>±X</td></tr><tr><td>X.X</td><td>±X</td></tr><tr><td>X.XX</td><td>±X</td></tr><tr><td>DIM</td><td>TOL</td></tr><tr><td>X.°</td><td>±X°</td></tr><tr><td>X.X°</td><td>±X°</td></tr><tr><td>Angle</td><td>TOL</td></tr></table>		Scale	1:1	TOLERANCE		X.	±X	X.X	±X	X.XX	±X	DIM	TOL	X.°	±X°	X.X°	±X°	Angle	TOL				Date	Name	Customer-No.	G
Scale		1:1																										
TOLERANCE																												
X.	±X																											
X.X	±X																											
X.XX	±X																											
DIM	TOL																											
X.°	±X°																											
X.X°	±X°																											
Angle	TOL																											
					Drawn	20.08.2009	Dean																					
					Approved	20.08.2009	Andy	ASSMANN WSW-No.	V5830																			
								Drawing-No.																				
H								ASS 0901 HS	rev01	H																		
								Replace	Sheet																			
	1	2	3	4	5	6	7																					