

## 10A, 35V - 150V Schottky Barrier Surface Mount Rectifier



### FEATURES

- AEC-Q101 qualified
- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
$I_F$	10	A
$V_{RRM}$	35 - 150	V
$I_{FSM}$	120	A
$T_{J MAX}$	150	°C
Package	TO-263AB (D <sup>2</sup> PAK)	
Configuration	Dual dies	

### APPLICATIONS

- Low voltage, high freq. inverter
- DC/DC converter
- Freewheeling diodes
- Reverse battery protection
- Car lighting


**TO-263AB (D<sup>2</sup>PAK)**


### MECHANICAL DATA

- Case: TO-263AB (D<sup>2</sup>PAK)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 1.37g (approximately)

ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)										
PARAMETER	SYMBOL	MBRS 1035 CTH	MBRS 1045 CTH	MBRS 1050 CTH	MBRS 1060 CTH	MBRS 1090 CTH	MBRS 10100 CTH	MBRS 10150 CTH	UNIT	
Marking code on the device		MBRS 1035CT	MBRS 1045CT	MBRS 1050CT	MBRS 1060CT	MBRS 1090CT	MBRS 10100CT	MBRS 10150CT		
Repetitive peak reverse voltage	$V_{RRM}$	35	45	50	60	90	100	150	V	
Reverse voltage, total rms value	$V_{R(RMS)}$	24	31	35	42	63	70	105	V	
Forward current	$I_F$	10								A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	$I_{FSM}$	120								A
Peak repetitive reverse surge current <sup>(1)</sup>	$I_{RRM}$	1								A
Peak repetitive forward current (Rated $V_R$ , Square wave, 20KHz)	$I_{FRM}$	10								A
Critical rate of rise of off-state voltage	$dv/dt$	10,000								V/μs

### Notes:

1.  $t_p = 2.0\mu\text{s}$ , 1.0KHz

<b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_A = 25^\circ\text{C}$ unless otherwise noted)									
<b>PARAMETER</b>	<b>SYMBOL</b>	<b>MBRS 1035 CTH</b>	<b>MBRS 1045 CTH</b>	<b>MBRS 1050 CTH</b>	<b>MBRS 1060 CTH</b>	<b>MBRS 1090 CTH</b>	<b>MBRS 10100 CTH</b>	<b>MBRS 10150 CTH</b>	<b>UNIT</b>
Junction temperature	$T_J$	-55 to +150					°C		
Storage temperature	$T_{STG}$	-55 to +150					°C		

<b>THERMAL PERFORMANCE</b>					
<b>PARAMETER</b>		<b>SYMBOL</b>	<b>TYP</b>	<b>UNIT</b>	
Junction-to-case thermal resistance		$R_{\theta JC}$	2	°C/W	

<b>ELECTRICAL SPECIFICATIONS</b> ( $T_A = 25^\circ\text{C}$ unless otherwise noted)						
<b>PARAMETER</b>		<b>CONDITIONS</b>	<b>SYMBOL</b>	<b>TYP</b>	<b>MAX</b>	<b>UNIT</b>
Forward voltage per diode <sup>(1)</sup>	MBRS1035CTH	$I_F = 5\text{A}, T_J = 25^\circ\text{C}$	$V_F$	-	0.70	V
	MBRS1045CTH			-	0.80	V
	MBRS1050CTH			-	0.85	V
	MBRS1060CTH			-	0.88	V
	MBRS1090CTH			-	0.80	V
	MBRS10100CTH	$I_F = 10\text{A}, T_J = 25^\circ\text{C}$	$V_F$	-	0.90	V
	MBRS10150CTH			-	0.95	V
	MBRS1035CTH			-	0.98	V
	MBRS1045CTH			-	0.57	V
	MBRS1050CTH			-	0.65	V
	MBRS1060CTH	$I_F = 5\text{A}, T_J = 125^\circ\text{C}$	$V_F$	-	0.75	V
	MBRS1090CTH			-	0.78	V
	MBRS10100CTH			-	0.67	V
	MBRS10150CTH			-	0.75	V
	MBRS1035CTH			-	0.85	V
	MBRS1045CTH	$I_F = 10\text{A}, T_J = 125^\circ\text{C}$	$V_F$	-	0.88	V
	MBRS1050CTH			-	0.65	V
	MBRS1060CTH			-	0.75	V
	MBRS1090CTH			-	0.78	V
	MBRS10100CTH			-	0.67	V
	MBRS10150CTH			-	0.75	V

<b>ELECTRICAL SPECIFICATIONS</b> ( $T_A = 25^\circ\text{C}$ unless otherwise noted)							
<b>PARAMETER</b>		<b>CONDITIONS</b>	<b>SYMBOL</b>	<b>TYP</b>	<b>MAX</b>	<b>UNIT</b>	
Reverse current @ rated $V_R$ per diode <sup>(2)</sup>	MBRS1035CTH MBRS1045CTH MBRS1050CTH MBRS1060CTH MBRS1090CTH MBRS10100CTH MBRS10150CTH	$T_J = 25^\circ\text{C}$	$I_R$	-	100	$\mu\text{A}$	
	MBRS1035CTH MBRS1045CTH	$T_J = 100^\circ\text{C}$		-	15	$\text{mA}$	
	MBRS1050CTH MBRS1060CTH			-	10	$\text{mA}$	
	MBRS1090CTH MBRS10100CTH MBRS10150CTH			-	-	$\text{mA}$	
	MBRS1035CTH MBRS1045CTH MBRS1050CTH MBRS1060CTH	$T_J = 125^\circ\text{C}$		-	-	$\text{mA}$	
	MBRS1090CTH MBRS10100CTH MBRS10150CTH			-	5	$\text{mA}$	






**Notes:**


1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms


<b>ORDERING INFORMATION</b>		
<b>ORDERING CODE<sup>(1)</sup></b>	<b>PACKAGE</b>	<b>PACKING</b>
MBRS10xCTH	TO-263AB (D <sup>2</sup> PAK)	800 / Tape & Reel

**Notes:**


1. "x" defines voltage from 35V(MBRS1035CTH) to 150V(MBRS10150CTH)

**CHARACTERISTICS CURVES**
 $(T_A = 25^\circ\text{C} \text{ unless otherwise noted})$ 
**Fig.1 Forward Current Derating Curve**

**Fig.2 Typical Junction Capacitance**

**Fig.3 Typical Reverse Characteristics**

**Fig.4 Typical Forward Characteristics**

**Fig.5 Maximum Non-Repetitive Forward Surge Current**


**CHARACTERISTICS CURVES** $(T_A = 25^\circ\text{C}$  unless otherwise noted)**Fig.6 Typical Transient Thermal Impedance**

**PACKAGE OUTLINE DIMENSIONS**
**TO-263AB (D<sup>2</sup>PAK)**


DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.44	4.70	0.175	0.185
A2	2.03	2.79	0.080	0.110
b	0.68	0.94	0.027	0.037
c	0.36	0.53	0.014	0.021
c2	1.14	1.40	0.045	0.055
D	8.25	9.25	0.325	0.364
E	-	10.50	-	0.413
e	2.41	2.67	0.095	0.105
H	14.60	15.88	0.575	0.625
L	2.29	2.79	0.090	0.110
L3	1.14	1.40	0.045	0.055

**SUGGESTED PAD LAYOUT**


Symbol	Unit (mm)	Unit (inch)
A	10.80	0.425
B	8.30	0.327
C	1.27	0.050
D	4.05	0.159
E	15.95	0.628
F	2.54	0.100
G	9.775	0.385

**MARKING DIAGRAM**


P/N = Marking Code  
 G = Green Compound  
 YWW = Date Code  
 F = Factory Code

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.