


GLASS BODY

24 AWG (0.020" \pm 0.002" DIAMETER),
TINNED CCS, 1.00" LONG MINIMUM



RESISTANCE @ +25°C = 50,000 Ω NOMINAL
ACCURACY (0 TO +100°C) = \pm 1.0°C
RESISTANCE/TEMPERATURE CURVE = "J"
TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
BETA "B" (0 TO +50°C) = 3,892°K NOMINAL
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (WELL STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +300°C

NONE	RELEASE TO PRODUCTION			04/30/03	DD
REV		REVISION RECORD		DATE	APP

SCALE	NONE	© COPYRIGHT			
DRAWN BY	DAN DANKERT	U.S. SENSOR CORP.			
DATE	04/30/03	714-639-1000 www.ussensor.com			
REV.	NONE	NTC THERMISTOR			
LAYER	0 OF 1	P/N 503JM1A			