

EH 22,5-C SS/ABS BK9005 - Upper housing part



2201253

<https://www.phoenixcontact.com/us/products/2201253>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Upper housing part, tall design, connection opening on one side, connection opening on one side, width: 22.6 mm, height: 75.26 mm, depth: 36.95 mm, color: black (similar RAL 9005)

Your advantages

- DIN rail or panel mounting for application-specific device attachment
- Easy design-in, thanks to variable housing form factor
- Complete flexibility, thanks to PCBs with horizontal, frontal, and orthogonal orientation to the front of the device
- Three cover versions for individual PCB connections
- Integration of a wide variety of PCB connection technologies for a functional device design

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2201253 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC12 |
| Product key | ACHCHC |
| GTIN | 4046356749961 |
| Weight per piece (including packing) | 13.23 g |
| Weight per piece (excluding packing) | 13.23 g |
| Customs tariff number | 84879090 |
| Country of origin | IN |

EH 22,5-C SS/ABS BK9005 - Upper housing part



2201253

<https://www.phoenixcontact.com/us/products/2201253>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|------------------------------|---|
| Product type | Upper housing part |
| Housing type | DIN rail housing |
| Housing series | EH |
| Product family | EH..ABS.. |
| Max. number of positions | 5 (pitch: 3.5 mm) |
| Type | Upper housing part, tall design, connection opening on one side |
| Ventilation openings present | no |

Dimensions

| | |
|---------------------------------|----------|
| Dimensional drawing | |
| Width | 22.6 mm |
| Height | 75.26 mm |
| Depth | 36.95 mm |
| Depth from base support surface | 19.95 mm |

Material specifications

| | |
|--|------------------|
| Color (Housing) | black (RAL 9005) |
| Flammability rating according to UL 94 | HB |
| Housing material | ABS |
| Surface characteristics | untreated |

Environmental and real-life conditions

| | |
|------------------------|-----------------------------|
| Vibration test | |
| Specification | IEC 60068-2-6:2007-12 |
| Frequency | 10 - 150 - 10 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.15 mm (10 Hz ... 58.1 Hz) |
| Acceleration | 2g (58.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h |
| Test directions | X-, Y- and Z-axis |

EH 22,5-C SS/ABS BK9005 - Upper housing part



2201253

<https://www.phoenixcontact.com/us/products/2201253>

Glow-wire test

| | |
|------------------|------------------------|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

Thermal stability / ball thrust test

| | |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 80 °C |
| Test duration | 1 h |
| Force | 20 N |

Mechanical strength / tumbling barrel

| | |
|----------------|---------------------|
| Specification | IEC 60998-1:2002-12 |
| Height of fall | 50 cm |
| Frequency | 10 |

Shocks

| | |
|--------------------------------|-----------------------------------|
| Specification | IEC 60068-2-27:2008-02 |
| Pulse shape | Half-sine |
| Acceleration | 15g |
| Shock duration | 11 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

Degree of protection (IP code)

| | |
|---------------|---|
| Specification | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |
|---------------|---|

Ambient conditions

| | |
|---|---|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 80 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 80 °C |
| Relative humidity (storage/transport) | 95 % |

PCB data

| | |
|-------------------|------|
| Type of PCB mount | Slot |
|-------------------|------|

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

Packaging specifications

| | |
|----------------------|---------------------|
| Type of packaging | packed in cardboard |
| Outer packaging type | Carton |

EH 22,5-C SS/ABS BK9005 - Upper housing part


2201253

<https://www.phoenixcontact.com/us/products/2201253>



Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

EH 22,5-C SS/ABS BK9005 - Upper housing part



2201253

<https://www.phoenixcontact.com/us/products/2201253>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201253>



UL Recognized

Approval ID: E240868

EH 22,5-C SS/ABS BK9005 - Upper housing part



2201253

<https://www.phoenixcontact.com/us/products/2201253>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190603 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

EH 22,5-C SS/ABS BK9005 - Upper housing part



2201253

<https://www.phoenixcontact.com/us/products/2201253>

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com