




Part Number : [2149221221](#)
Product Description : Pre-Crimped Lead PicoBlade
Male-to-PicoBlade Male, Tin (Sn) Plating, 75.00mm
Length, 26 AWG, Red
Series Number : 214922
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents and Resources

Drawings

- [2149221221 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	214922
Description	Pre-Crimped Lead PicoBlade Male-to-PicoBlade Male, Tin (Sn) Plating, 75.00mm Length, 26 AWG, Red
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	PicoBlade
UPC	193264503025

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Cable Length	75.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Male-Male
Material - Metal	Phosphor Bronze

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.237/g
Packaging Type	Bag
Plating min - Mating	0.889µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	26

Mates With / Use With

Use with Part(s)

Description	Part Number
PicoBlade Single Row Plug Housings	<u>51047</u>

This document was generated on May 23, 2026