

**Part Number :** [399800404](#)


**Product Description :** 5.08mm Pitch Beau Eurostyle Surface Mount Compatible Locking Header, 4 Circuits

**Series Number :** 39980

**Status :** Obsolete

**Product Category :** Terminal Blocks and Barrier Strip

**Engineering Part Number :** 981504



---

## Documents and Resources

[399800404 stp.zip](#)


### Specifications

[PS-39980-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Obsolete
Category	Terminal Blocks and Barrier Strip
Series	39980
Description	5.08mm Pitch Beau Eurostyle Surface Mount Compatible Locking Header, 4 Circuits
Application	Wire-to-Board
Comments	Gold plating available
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	800753316614

#### Agency

UL	E48521
----	--------

#### Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

#### Physical

Circuits (Loaded)	4
Color - Resin	Black
Entry Angle	N/A
Flammability	94V-0
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Material - Resin	Nylon
Net Weight	3.626/g
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.81mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Shrouded	Unshrouded
Stackable	No
Temperature Range - Operating	140°C
Wire Size (AWG)	N/A

---

This document was generated on Apr 20, 2026

Obsoleted