


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

Customer Drawing


REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	08/22/08	IP
2	HK--	Add 50Pin Drawing	09/06/13	IP
3	HK--	Add dimension "REF 6.0" and "REF 5.9"	10/20/16	IP

D-SUB TECHNICAL DATA

SHELL: Steel, 100u" Tin over 50u" min nickel over 50u" min Copper
BODY : PBT, UL 94V-0, Color:Black
CONTACTS: Copper alloy.
Gold flash over 50u" min nickel on contact area.
100u" min tin over 50u" min nickel on solder area.
BOARDLOCK: Brass, Tin Plated.
ELECTRICAL: Contact Resistance : 20 mΩ Max
Insulation Resistance : 1000 MΩ
Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
Current Rating : 3AMP
Voltage Rating : 250 VAC/rms 60Hz
MARKING: Amphenol...(Series No.)
Commercial reference
Manufacturing date



Positions	A	B	C	E	F
09	30.81	24.99	16.92	11.08	19.20
15	39.20	33.30	25.25	19.39	27.70
25	53.04	47.04	38.96	33.24	41.10
37	69.40	63.50	55.42	49.86	57.30



PRODUCT CODE

L 717 SD X H XX P OL2 RM5

L: RoHS Compliance

717:
tinned shell + dimples
for plug

Series:
SD = Standard density

Shell size::
E = 9
A = 15
B = 25
C = 37
D = 50

Rear mounting option:
H = 4-40 rear insert

Front mounting option:
RM5 = Threaded standoff +
boardlock

Termination:
Straight, for PCB mount

Contact type:
P = Plug

Configuration:
09,15,25,37,50

UNLESS OTHERWISE SPECIFIED TOLERANCES	
U.S.	METRIC
.X +/-	0.50
.XX +/-	0.30
.XXX +/-	0.20
FRACTIONS +/-	
ANGLES +/-	5°

FOR MATERIALS AND FINISHES
SEE NOTES

REMOVE SHARP EDGES


DIMENSIONS

U.S.	INCHES
METRIC	MM

APPROVAL		DATE
DRAWN	Peking Liu	10/20/16
CHECKED	Tony Tang	10/20/16
CHECKED		

DRAWING FILE :

ANGLE OF PROJECTION



TITLE
D-SUB connectors, SD series

SIZE	DRAWING NO.	REV.
A4	L717SDXHXXPOL2RM5	3
SCALE	SHEET 1 OF 1	
NONE		