






B



P.C.B. RECOMMENDED HOLE LAYOUT  
SEEN FROM COMPONENT SIDE  
ALL CENTERLINE DIMENSIONS ARE BASIC.

RoHS



1

| DATE    | REV | ECN   | APP'D. BY |
|---------|-----|-------|-----------|
| 1-13-15 | A4  | 10185 | TRM       |
| 3-8-16  | A5  | 10591 | TRM       |
| 7-10-23 | B0  | 12210 | JE        |
|         |     |       |           |

- NOTES:
- CONNECTOR MATERIALS:  
HOUSING: HI-TEMP, UL94 V-0  
CONTACTS/SHIELD: COPPER ALLOY  
SHIELD PLATING: NICKEL OR "REFLOW" TIN  
CONTACT PLATING: SELECTIVE GOLD OR EQUIVALENT  
IN THE CONTACT AREA  
SEE CHART FOR PART NUMBER
  - FOR PRODUCT SPECIFICATIONS SEE PR022-01.
  - RATED AT MAX. 260°C FOR MAX. 10 SECS.
  - DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.

|                                   |              |
|-----------------------------------|--------------|
| 30 MICRO-INCHES [0.76um]          | SS64100-042F |
| CONTACT PLATING<br>IN MATING AREA | PART NUMBER  |

|                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| THIRD ANGLE PROJECTION<br>                                                                                  | <br>11118 Susquehanna Trail South<br>Glen Rock, PA 17327-9199<br>(717) 235-7512<br><a href="http://www.stewartconnector.com">http://www.stewartconnector.com</a>                                                                                                                                                                                                                                                                           |
| DO NOT SCALE DRAWING<br>DRAWING IS SUBJECT TO<br>CHANGE WITHOUT NOTICE                                      | TITLE: TEN CONTACT, TEN POSITION, SHIELDED JACK                                                                                                                                                                                                                                                                                                                                                                                            |
| DIMENSIONS: INCHES [METRIC]<br>UNLESS OTHERWISE SPECIFIED<br>TOLERANCES ARE ±.005 [0.13]<br>ANGLES ARE ± 1° | THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON<br>ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF<br>STEWART CONNECTOR AND SHALL NOT BE REPRODUCED,<br>COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN<br>CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS<br>MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE<br>VISIT: <a href="http://BELFUSE.COM/STEWART/STEWART_PATENTS/">HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/</a> |
| SHEET NO. 1 OF 1                                                                                            | DRN BY: RVO DATE 02-03-05<br>APPD BY: DHG DATE 02-22-05<br>DWG NO. CT640008F REV. B0                                                                                                                                                                                                                                                                                                                                                       |

B

A

2

1