

**Part Number :** [190670114](#)


**Product Description :** NylaKrimp Funnel Entry Ring  
Tongue Terminal for 2/0 AWG Wire, Stud Size  
1/2" (M12), Carton

**Series Number :** 19067

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Part Number :** J-987-12



---

## Documents and Resources

### Drawings

[190670114\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-19902-013-001.pdf](#)

[PS-19902-016-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/2" (M12), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	NylaKrimp
Style	Ring
Type	Ring Terminal
UPC	800753067073

### Agency

UL	E32244
----	--------

### Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Packaging Type	Carton
Plating min - Mating	2.540µm

Plating min - Termination	2.540μm
Stud Size	1/2" (M12)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	19.43mm max.
Wire Size (AWG)	2/0

---

## Application Tooling

---

This document was generated on Apr 11, 2026