

Specification Sheet

Part Number: 156-00552



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole

Edge Clip provides low insertion force and high extraction force ideal for assembly environments

2-Piece Cable Tie with EC10 Edge Clip, 8.0" Long, 0.04 - 0.12" Panel Thickness , 50 lbs, PA66HS, Black, 500/bg

Article Number 156-00552

Type T50REC10

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Two-Piece Edge Clip with Cable Tie assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure, and the pull-off strength is high due to the integrated metal clamp that holds the edge clip in place.

Short Description 2-Piece Cable Tie with EC10 Edge Clip, 8.0" Long, 0.04 - 0.12" Panel Thickness , 50 lbs, PA66HS, Black, 500/bg

Global Part Name T50REC10-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	200.0
Fixation Method	Edge Clip
Identification Plate Position	none
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Height H (Imperial)	0.05
Height H (Metric)	1.2
Panel Thickness Min (Imperial)	0.04

Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Foot Part Material	PA66HIRHS
Material Shortcut	PA66HIRHS PA66HS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)