



**Part Number :** [1200878737](#)

**Product Description :** Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Female (90°), 24 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length

**Series Number :** 120087

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 445031B41M050



---

## Documents and Resources

### Drawings

[1200878737\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## CE - Declaration of Conformity

## UKCA - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Female (90°), 24 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Double Ended
UPC	889056074230

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC / 36V DC

### Physical

Cable Diameter	5.30mm (.209")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	B-Coded
LED Indicator	None

Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	555.000/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	24

---

This document was generated on Dec 30, 2025