

Data sheet

PT116xxHBBN Typ 230

Page 1/6

P/N
312301xx

xx=number of poles


2019/10/28

Version: S


Illustrations



Dimensional drawing



Drill pattern



See enlarged drawings at the end of document

Product specification

- pin header, solderable
- centerline 5.08 mm, direction of connection 90°
- closed ends
- color black
- codeable

Data sheet

PT116xxHBBN Typ 230

Page 2/6

P/N
312301xx

xx=number of poles

2019/10/28

Version: S

Technical Data

General Data

Solder pin length	3.45 mm		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 600		
clearance/creepage dist.	4.08 mm		
protection category	IP00		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	320 V	800 V	800 V
Rated test voltage	4 kV	4 kV	4 kV

Approvals

 V / A	300 / 15
approval UL - File No.	E121004
 1.5 mm ²	320 V / 4 kV / 13.5 A / 1.0 x 1.0 mm

Material

insulating material	PA66
flammability class	V0
contact pin material	CuFe
contact pin surface	Ni + Ag
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12
Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13
REACH - substance (SVHC)	none

Climatic Data

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

Tolerance	ISO 2768 -mH
Solderability	Acc. to JEDEC JESD22-B102E 245°C/5s

Accessories

P/N	Designation
700024-01-9	700024
700523-0157	Geh_Kappe_swg_Block

U | Contact

Data sheet

PT116xxHBBN Typ 230

Page 4/6

P/N

312301xx

xx=number of poles

2019/10/28

Version: S


Counterpart of

P/N	Designation
312131	RP036xxHBLC Typ 213
312141	RP036xxHBLD Typ 214
312491	RP016xxVBLC Typ 249
312501	RP016xxSBLC Typ 250
ASP046	SP046xxVBNC ASP046



Illustrations

Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 6.28 \text{ mm} [0.247]$

Illustrations

Drill pattern

