





MASTER KEYWAY



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	Nov-10-17	Nick	TOMMY
A2	-	UPDATE CABLE OD RANGE	Feb-07-2018	Nick	TOMMY
A3	-	UPDATE DRAWING	Mar-26-2018	White	Tommy
A4	-	UPDATE NOTES	Oct-18-2018	Blink	Tommy



NOTES : (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL :

SHELL : THERMOPLASTIC , UL94 V-0.
 INSERT : THERMOPLASTIC , UL94 V-0.
 COUPLING NUT : THERMOPLASTIC , UL94 V-0.
 O-RING : NBR OR SILICONE RUBBER.
 WASHER : SILICONE RUBBER.
 BACK SHELL : THERMOPLASTIC , UL94 V-0.
 CLAMP NUT : THERMOPLASTIC , UL94 V-0.
 CLAMP RING : THERMOPLASTIC , UL94 V-0.
 CABLE SEAL : EPDM.

2. SPECIFICATIONS :


2.1 RATED CURRENT : 45A (MAX).
 2.2 RATED VOLTAGE : 600V(AC/DC).
 2.3 OPERATING TEMPERATURE : SEE TABLE.
 2.4 DIELECTRIC WITHSTANDING VOLTAGE : LESS THAN
 2 MILLIAMPS CURRENT LEAKAGE@2500 VOLTS AC.
 2.5 INSULATION RESISTANCE : 5000 MEGOHMS MIN.
 2.6 IP CLASS : IP67 AND IP69K IN THE MATED CONDITION,
 WIRE SEALS FULLY POPULATED.
 2.7 MATING CYCLES DURABILITY : 500 CYCLES MIN.
 2.8 RoHS COMPLIANT.

3. SUITABLE CONTACTS : 8# CONTACT.

CONTACT SIZE	CONTACT PN	WIRE RANGE
8#	MP10A23x-25	16 - 14AWG
	MP10A23x-63	12 - 10AWG
	MP10A23x-10	8 AWG

IN THE CONTACT PN,"x" DENOTE DIFFERENT PLATING.

4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



DIMENSION ØA	CABLE OD RANGE
12.3MM	6.0-12.0MM
14.3MM	9.0-14.0MM

KEY	PART NUMBER	
	-40°C ~ +105°C	-40°C ~ +125°C
N	RTS6BS14N3P	RTS6BS14N3P03

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64 2 PL DEC ±0.15 Angles ±1° 3 PL DEC ±0.08 3) Note reference =			
SIGNATURES		DATE	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 ECO-MATE, PLUG, BACK SHELL, SIZE 14,3POS,PIN
DRAWN: Blink		Oct-18-2018	
CHECKED: Tod		Oct-18-2018	
ENGINEER:			
APPROVAL: Tommy		Oct-18-2018	THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.
MATERIAL SPECIFICATIONS:			
PROCESS SPECIFICATIONS:			
NEXT ASSY:			
CUSTOMER:			SIZE TYPE B C- SCALE: NONE
DWG NO.			
REVISION			A4 SHEET 1 OF 1
PART NUMBER			

TITLE: ECO-MATE PLUG BACK SHELL SIZE 14,3POS,PIN
 DWG NO.: RTS6BS14*3Pxx
 REV: A4
 SH: 1
 OF: 1

ecomate® RM, RSSM and Aquarius™ Series
Size 3.6mm Contact & Tooling Options (1403 Insert Arrangement)

Machined, Crimp Contacts						
Part Number		Contact Size (AWG)	Wire Range (mm²)	Male Contact For Use w End Cap	Female Contact For Use w End Cap	Plating
Male	Female					
MP10A23T-10	MS10A23T-10	8AWG	10.0 mm²	No	No	Tin
MP10A23S-10	MS10A23S-10	8AWG	10.0 mm²	No	No	Silver
MP10A23F-10	MS10A23F-10	8AWG	10.0 mm²	No	No	Gold Flash
MP10A23G5-10	MS10A23G5-10	8AWG	10.0 mm²	No	No	Gold 5µ"
MP10A23G10-10	MS10A23G10-10	8AWG	10.0 mm²	No	No	Gold 10µ"
MP10A23G15-10	MS10A23G15-10	8AWG	10.0 mm²	No	No	Gold 15µ"
MP10A23G30-10	MS10A23G30-10	8AWG	10.0 mm²	No	No	Gold 30µ"
MP10A23S-63	MS10A23S-63	10-12AWG	4.0-6.0 mm²	No	No	Silver
MP10A23F-63	MS10A23F-63	10-12AWG	4.0-6.0 mm²	No	No	Gold Flash
MP10A23S-63	MS10A23S-63W	10-12AWG	4.0-6.0 mm²	No	Yes	Silver
MP10A23F-63	MS10A23F-63W	10-12AWG	4.0-6.0 mm²	No	Yes	Gold Flash
MP10A23TL	MS10A23T	10-12AWG	3.0-6.0 mm²	Yes	Yes	Tin
MP10A23SL	MS10A23S	10-12AWG	3.0-6.0 mm²	Yes	Yes	Silver
MP10A23FL	MS10A23F	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold Flash
MP10A23G5L	MS10A23G5	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 5µ"
MP10A23G10L	MS10A23G10	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 10µ"
MP10A23G15L	MS10A23G15	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 15µ"
MP10A23G30L	MS10A23G30	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 30µ"
MP10A23S-25	MS10A23S-25	14-16AWG	1.5-2.5 mm²	No	No	Silver
MP10A23F-25	MS10A23F-25	14-16AWG	1.5-2.5 mm²	No	No	Gold Flash
MP10A23S-25	MS10A23S-25W	14-16AWG	1.5-2.5 mm²	No	Yes	Silver
MP10A23F-25	MS10A23F-25W	14-16AWG	1.5-2.5 mm²	No	Yes	Gold Flash

Machined, Tooling	
Part Number	Description
QXRT08	Contact Extraction Tool, # 8 (Ø 3.6mm) Contact
M300BT	Hand Crimper
WA27-300BT-EP	Pneumatic Crimper
TP968	Locator M3200BT and WA27-300BT-EP

Plating Options	
Symbol	Plating
T	Tin Plated (for Stamped & Formed Contacts)
S	Silver Plated 5Um (for Machined Contacts)
F	Gold Plated
G5	Gold Plated (Thickness 5µ")
G10	Gold Plated (Thickness 10µ")
G15	Gold Plated (Thickness 15µ")
G30	Gold Plated (Thickness 30µ")