



Part Number : [459844924](#)

Product Description : EXTreme LPHPower Receptacle Header, Right-Angle, 4 Power Contacts, Select Gold (Au) Plating, for 2.36mm Thick PC Board, with Guide Posts and Press-fit Plastic Pegs

Series Number : 45984

Status : Active

Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

[459844924 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


[SYM-45984-4914-001.zip](#)

Specifications

[PS-45984-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	45984
Description	EXTreme LPHPower Receptacle Header, Right-Angle, 4 Power Contacts, Select Gold (Au) Plating, for 2.36mm Thick PC Board, with Guide Posts and Press-fit Plastic Pegs
Application	Board-to-Board, Power
Component Type	PCB Receptacle, Receptacle
Product Name	EXTreme LPHPower
UPC	800756651675

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	30.0A
Grounding to PCB	No

Voltage - Maximum	250V AC (RMS)/DC (Power)
-------------------	--------------------------

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.846/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
PC Tail Length	3.60mm
Pitch - Mating Interface	12.00mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Polarized to PCB	No
(p)ower-(s)ignal Configuration	4p - 0s
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	15
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	230

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme LPHPower Right-Angle Plugs	<u>45985</u>
Mates With	1.57mm Card Edge

This document was generated on Dec 31, 2025