




Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Material: **Copper Alloy**

Automotive Connector Accessory Type: **Fixation**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Fixation
-------------------------------------	----------

Body Features

Primary Product Material	Copper Alloy
--------------------------	--------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Box
Packaging Quantity	4500

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247)



Does not contain REACH SVHC







Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2381609-2 OCEAN-2.0-APPLICATOR-S-203SP173O-SSA	 TE Part # 2371101-3 MATENET,INLINE COUPLER ASSY, COD C	 TE Part # 2367280-2 1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD B	 TE Part # 2367280-1 1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD A
 TE Part # 2236905-1 NANO TAB 0.5X0.4,TERMINAL	 TE Part # CAT-M8793-T273 MQS, RECEPTACLE AND TAB	 TE Part # 2381607-2 OCEAN-2.0-APPLICATOR-S-203SP173O-SSA	 TE Part # 2236905-3 NANO TAB 0.5X0.4,TERMINAL
 TE Part # 2302451-1 MATENET, MALE INSERT MODUL	 TE Part # 2371101-9 MATENET,INLINE COUPLER ASSY, COD Z	 TE Part # 2371101-1 MATENET INLINE COUPLER ASSY, COD A	 TE Part # 2371101-2 MATENET,INLINE COUPLER ASSY, COD B



TE Part # 2302450-1
MATENET, FEMALE INSERT MODUL, BLACK

TE Part # 2367280-3
1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD C

TE Part # 2367280-9
1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD Z

TE Part # 2371101-7
MATENET,INLINE COUPLER ASSY, COD J

TE Part # 2367280-7
1POS,NANOMQS,TAB HSG ASSY, UNSLD,COD J

Customers Also Bought

TE Part #1-2236905-1
NANO TAB 0.5X0.4,TERMINAL

TE Part #2306868-1
2P,MATE-AX,SOC HSG ASSYCOD A

TE Part #2385337-3
HOUSING, CLIP SLOT, 1POSITION, FAKRA

TE Part #2394145-1
Matenet inline 1p with clip, cod A

TE Part #2302451-1
MATENET, MALE INSERT MODUL

TE Part #2141360-2
HANDHOLD,CRIMP BUSHING

TE Part #2333538-1
MATENET 2X3 PORT PLUG ASSEMBLY,CONN KIT

TE Part #2326911-1
COAX,SOC HSG,UNSLD,180DEG

TE Part #2302450-1
MATENET, FEMALE INSERT MODUL, BLACK

TE Part #2439510-1
FAKRA Terminal, Pin Contact,RG174

Documents



Product Drawings

MATENET, FIXATION ELEMENT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2302452-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2302452-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2302452-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English