



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE30140 thru NTE30151 Discrete LED Indicators 3mm (T-1) Package Type

Features:

- All 3mm Types Available in Multiple Colors and Lens Types:

Color	Water Clear	White Diffused
Red	NTE30140	NTE30146
Green	NTE30141	NTE30147
Blue	NTE30142	NTE30148
White	NTE30143	NTE30149
Pink	NTE30144	NTE30150
UV/Purple	NTE30145	NTE30151

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Power Dissipation, P_D	80mW
Peak Forward Current (1/10th Duty Cycle, 0.1ms Pulse Width), I_{FM}	100mA
Continuous Forward Current, I_F	25mA
Derating Linear from $+30^\circ\text{C}$	0.8mA/ $^\circ\text{C}$
Reverse Voltage, V_R	5V
Operating Temperature Range, T_{opr}	-20° to $+80^\circ\text{C}$
Storage Temperature Range, T_{stg}	-30° to $+100^\circ\text{C}$
Lead Temperature (During Soldering, 1.6mm from Body, 5sec Max), T_L	$+260^\circ\text{C}$

Electrical Optical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Forward Voltage NTE30140, NTE30146	V_F	$I_F = 20\text{mA}$	2.0	–	2.2	V
All Others			3.0	–	3.2	V
Luminous Intensity NTE30140	I_V	$I_F = 20\text{mA}$	800	–	1000	mcd
NTE30141			5000	–	7000	mcd
NTE30142, NTE30149			1000	–	1500	mcd
NTE30143			4000	–	6000	mcd
NTE30144			300	–	400	mcd
NTE30145			100	–	150	mcd
NTE30146, NTE30148			100	–	120	mcd
NTE30147			1000	–	2000	mcd
NTE30150			60	–	80	mcd
NTE30151			40	–	50	mcd

Rev. 12-21



Electrical Optical Characteristics (Cont'd): ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Peak Emission Wavelength NTE30140, NTE30146	λ_p		620	625	630	nm
NTE30141, NTE30147			515	–	525	nm
NTE30142, NTE30148			460	–	470	nm
NTE30143, NTE30149			8000	–	12000	K
NTE30145, NTE30151			390	–	410	nm
Half Intensity Angle	$2\theta_{1/2}$		–	30	–	deg

