

## 500mW, 5% Tolerance SMD Zener Diodes

### FEATURES

- Wide zener voltage range selection: 2.4V to 51V
- $V_Z$  tolerance selection of  $\pm 5\%$
- Moisture sensitivity level: level 1, per J-STD-020
- Compliant to RoHS directive 2011/65/EU and in accordance to WEEE 2002/96/EC

| KEY PARAMETERS             |            |                    |
|----------------------------|------------|--------------------|
| PARAMETER                  | VALUE      | UNIT               |
| $V_Z$                      | 2.4-51     | V                  |
| $P_D$                      | 500        | mW                 |
| $V_F$ at $I_F=10\text{mA}$ | 0.9        | V                  |
| $T_J$ Max.                 | 150        | $^{\circ}\text{C}$ |
| Package                    | SOD-123F   |                    |
| Configuration              | Single die |                    |

### APPLICATIONS

- Low voltage stabilizers or voltage references
- Adapters
- On-board DC/DC converter



### MECHANICAL DATA

- Case: SOD-123F
- Molding compound meets UL 94 V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Polarity: Indicated by cathode band
- Weight:  $8.85 \pm 0.5\text{mg}$  (approximately)



### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^{\circ}\text{C}$ unless otherwise noted)

| PARAMETER                           | SYMBOL    | VALUE       | UNIT               |
|-------------------------------------|-----------|-------------|--------------------|
| Forward voltage @ $I_F=10\text{mA}$ | $V_F$     | 0.9         | V                  |
| Power dissipation                   | $P_D$     | 500         | mW                 |
| Junction temperature range          | $T_J$     | -65 to +150 | $^{\circ}\text{C}$ |
| Storage temperature range           | $T_{STG}$ | -65 to +150 | $^{\circ}\text{C}$ |

### THERMAL PERFORMANCE

| PARAMETER                              | SYMBOL          | TYP | UNIT                 |
|----------------------------------------|-----------------|-----|----------------------|
| Junction-to-ambient thermal resistance | $R_{\theta JA}$ | 330 | $^{\circ}\text{C/W}$ |

**ELECTRICAL SPECIFICATIONS** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)

| PART<br>NUMBER | MARKING<br>CODE | ZENER VOLTAGE  |      |       | TEST<br>CURRENT | REGULAR<br>IMPEDANCE |                   | TEST<br>CURRENT | LEAKAGE<br>CURRENT |     |
|----------------|-----------------|----------------|------|-------|-----------------|----------------------|-------------------|-----------------|--------------------|-----|
|                |                 | $V_Z @ I_{ZT}$ |      |       | $I_{ZT}$        | $Z_{ZT} @ I_{ZT}$    | $Z_{ZK} @ I_{ZK}$ | $I_{ZK}$        | $I_R @ V_R$        |     |
|                |                 | V              |      |       | mA              | $\Omega$             | $\Omega$          | mA              | $\mu\text{A}$      | V   |
|                |                 | Min.           | Nom. | Max.  |                 | Max.                 | Max.              |                 | Max.               |     |
| MMSZ5221B      | Z2V4            | 2.28           | 2.4  | 2.52  | 20              | 30                   | 1200              | 0.25            | 100                | 1   |
| MMSZ5225B      | Z3V0            | 2.85           | 3.0  | 3.15  | 20              | 29                   | 1600              | 0.25            | 50                 | 1   |
| MMSZ5226B      | Z3V3            | 3.14           | 3.3  | 3.47  | 20              | 28                   | 1600              | 0.25            | 25                 | 1   |
| MMSZ5227B      | Z3V6            | 3.42           | 3.6  | 3.78  | 20              | 24                   | 1700              | 0.25            | 15                 | 1   |
| MMSZ5228B      | Z3V9            | 3.71           | 3.9  | 4.10  | 20              | 23                   | 1900              | 0.25            | 10                 | 1   |
| MMSZ5229B      | Z4V3            | 4.09           | 4.3  | 4.52  | 20              | 22                   | 2000              | 0.25            | 5                  | 1   |
| MMSZ5230B      | Z4V7            | 4.47           | 4.7  | 4.94  | 20              | 19                   | 1900              | 0.25            | 5                  | 2   |
| MMSZ5231B      | Z5V1            | 4.85           | 5.1  | 5.36  | 20              | 17                   | 1600              | 0.25            | 5                  | 2   |
| MMSZ5232B      | Z5V6            | 5.32           | 5.6  | 5.88  | 20              | 11                   | 1600              | 0.25            | 5                  | 3   |
| MMSZ5234B      | Z6V2            | 5.89           | 6.2  | 6.51  | 20              | 7                    | 1000              | 0.25            | 5                  | 4   |
| MMSZ5235B      | Z6V8            | 6.46           | 6.8  | 7.14  | 20              | 5                    | 750               | 0.25            | 3                  | 5   |
| MMSZ5236B      | Z7V5            | 7.13           | 7.5  | 7.88  | 20              | 6                    | 500               | 0.25            | 3                  | 6   |
| MMSZ5237B      | Z8V2            | 7.79           | 8.2  | 8.61  | 20              | 8                    | 500               | 0.25            | 3                  | 6.5 |
| MMSZ5239B      | Z9V1            | 8.65           | 9.1  | 9.56  | 20              | 10                   | 600               | 0.25            | 3                  | 7   |
| MMSZ5240B      | Z10V            | 9.50           | 10   | 10.50 | 20              | 17                   | 600               | 0.25            | 3                  | 8   |
| MMSZ5241B      | Z11V            | 10.45          | 11   | 11.55 | 20              | 22                   | 600               | 0.25            | 2                  | 8.4 |
| MMSZ5242B      | Z12V            | 11.40          | 12   | 12.60 | 20              | 30                   | 600               | 0.25            | 1                  | 9.1 |
| MMSZ5243B      | Z13V            | 12.35          | 13   | 13.65 | 9.5             | 13                   | 600               | 0.25            | 0.5                | 9.9 |
| MMSZ5245B      | Z15V            | 14.25          | 15   | 15.75 | 8.5             | 16                   | 600               | 0.25            | 0.1                | 11  |
| MMSZ5246B      | Z16V            | 15.20          | 16   | 16.80 | 7.8             | 17                   | 600               | 0.25            | 0.1                | 12  |
| MMSZ5248B      | Z18V            | 17.10          | 18   | 18.90 | 7.0             | 21                   | 600               | 0.25            | 0.1                | 14  |
| MMSZ5250B      | Z20V            | 19.00          | 20   | 21.00 | 6.2             | 25                   | 600               | 0.25            | 0.1                | 15  |
| MMSZ5251B      | Z22V            | 20.90          | 22   | 23.10 | 5.6             | 29                   | 600               | 0.25            | 0.1                | 17  |
| MMSZ5252B      | Z24V            | 22.80          | 24   | 25.20 | 5.2             | 33                   | 600               | 0.25            | 0.1                | 18  |
| MMSZ5254B      | Z27V            | 25.65          | 27   | 28.35 | 4.6             | 41                   | 600               | 0.25            | 0.1                | 21  |
| MMSZ5256B      | Z30V            | 28.50          | 30   | 31.50 | 4.2             | 49                   | 600               | 0.25            | 0.1                | 23  |
| MMSZ5257B      | Z33V            | 31.35          | 33   | 34.65 | 3.8             | 58                   | 700               | 0.25            | 0.1                | 25  |
| MMSZ5258B      | Z36V            | 34.20          | 36   | 37.80 | 3.4             | 70                   | 700               | 0.25            | 0.1                | 27  |
| MMSZ5259B      | Z39V            | 37.05          | 39   | 40.95 | 3.2             | 80                   | 800               | 0.25            | 0.1                | 30  |
| MMSZ5260B      | Z43V            | 40.85          | 43   | 45.15 | 3.0             | 93                   | 900               | 0.25            | 0.1                | 33  |
| MMSZ5261B      | Z47V            | 44.65          | 47   | 49.35 | 2.7             | 105                  | 1000              | 0.25            | 0.1                | 36  |
| MMSZ5262B      | Z51V            | 48.45          | 51   | 53.55 | 2.5             | 125                  | 1100              | 0.25            | 0.1                | 39  |

**Notes:**

1. The zener voltage ( $V_Z$ ) is tested under pulse condition of 30ms.
2. The device numbers listed have a standard tolerance on the normal zener voltage of  $\pm 5\%$ .
3. For detailed information on price, availability and delivery of normal zener voltages between the voltages shown and tighter voltage tolerances, contact your nearest Taiwan Semiconductor representative.
4. The zener impedance is derived from the 60-cycle ac voltage, which results when an ac current having a rms value equal to 10% of the DC zener current ( $I_{ZT}$  or  $I_{ZK}$ ) is superimposed to  $I_{ZT}$  or  $I_{ZK}$ .

| <b>ORDERING INFORMATION</b>         |                |                |
|-------------------------------------|----------------|----------------|
| <b>ORDERING CODE</b><br>(Note 1, 2) | <b>PACKAGE</b> | <b>PACKING</b> |
| MMSZ52xxB RHG                       | SOD-123F       | 3K / 7" Reel   |
| MMSZ52xxB RH                        | SOD-123F       | 3K / 7" Reel   |


**Note:**

1. "xxx" defines voltage from 2.4V (MMSZ5221B) to 51V (MMSZ5262B)
2. "G" means green compound (halogen free)


## CHARACTERISTICS CURVES

( $T_A = 25^\circ\text{C}$  unless otherwise noted)


**Fig.1 Typical Forward Voltage**




**Fig. 2 Zener Breakdown Characteristics**



**Fig. 3 Zener Breakdown Characteristics**




**Fig.4 Admissible Dissipation VS. Ambient Temperature**




## CHARACTERISTICS CURVES

( $T_A = 25^\circ\text{C}$  unless otherwise noted)

**Fig.5 Typical Capacitance**




**Fig.6 Effect of Zener Voltage on Impedance**




## PACKAGE OUTLINE DIMENSION

SOD-123F



| DIM. | Unit (mm) |      | Unit (inch) |       |
|------|-----------|------|-------------|-------|
|      | Min       | Max  | Min         | Max   |
| A    | 1.50      | 1.70 | 0.059       | 0.067 |
| B    | 3.30      | 3.90 | 0.130       | 0.154 |
| C    | 0.50      | 0.70 | 0.020       | 0.028 |
| D    | 2.50      | 2.70 | 0.098       | 0.106 |
| E    | 0.80      | 1.15 | 0.031       | 0.045 |
| F    | 0.05      | 0.20 | 0.002       | 0.008 |

## SUGGEST PAD LAYOUT



| DIM. | Unit (mm) | Unit (inch) |
|------|-----------|-------------|
|      | Typ.      | Typ.        |
| C    | 2.86      | 0.113       |
| G    | 1.52      | 0.060       |
| X    | 1.34      | 0.053       |
| X1   | 4.20      | 0.165       |
| Y    | 1.80      | 0.071       |

## Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.