



Part Number : [350689702](#)
Series Number : 35068
Status : Active - Proprietary
Product Category : Quick Disconnects



Specifications

- [PK-35068-001-001.pdf](#)
- [PS-35189-002-001.pdf](#)
- [PS-35189-004-001.pdf](#)
- [PS-35817-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active - Proprietary
Category	Quick Disconnects
Series	35068
Description	MP-Lock Quick Disconnect, Female, for 22-20 AWG (0.52-0.33mm ²), Metal Strip, Tab 4.75 x 0.51mm, Pre-Tin Plated
Product Name	MP-Lock
Type	Standard Quick Disconnect
UPC	800754321174

Agency

CSA	LR95446
UL	E92853

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Open
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	Yes
Net Weight	0.386/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	Yes
Tab Thickness	0.51mm

Tab Width	4.75mm
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size (AWG)	20, 22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
4.75mm Tab MP-Lock Housings	<u>35189</u>
MP-Lock Receptacle Housings	<u>35817</u>

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator for MP-Lock™ Quick Disconnect Terminals, Female, 22-20 AWG	<u>638019000</u>

This document was generated on Sep 18, 2025