

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.






ORIGINAL




REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
A	NE-15065	RELEASE REVISION	06/08/2015	Roger Tsai

NOTES:


1. CONTACT: COPPER ALLOY, 100u" MIN. MATTE TIN OR FULL GOLD FLASH OVER 50μ" MIN. NICKEL UNDER-PLATING OVERALL
2. THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS MATERIAL PER DIRECTIVE 2011/65/EU FOR RoHS.
3. PACKING MUST BE PER Amphenol PACKING SPECIFICATION PKS-0001
4. USED WITH G878HXX2T1HR HOUSING.
5. PRODUCT SPECIFICATION REFER TO : PS-7560.
6. TEST SUMMARY REFER TO : TS-7560.
7. WIRE RANGE: AWG#26~#30.
8. INSULATION O.D.: ϕ 0.70~1.00MM.



Section A-A



Section B-B



Section C-C

PART NO. G878C X 12T1EU

CONTACT FINISH
0: 100u" MATTE TIN
1: FULL GOLD FLASH
2: 15u" GOLD

TOLERANCE		APPROVALS		DATE	TITLE G878 SERIES, SOCKET CRIMP TYPE CONTACT FOR 1.25 PITCH				Amphenol® Amphenol Corporation Amphenol Taiwan Corporation			
X. X.X ±0.30 X.XX ±0.20 X.XXX ±0.10		DRAWN Aqua Chou	06/08/2015									
		CHECKED Roger Tsai	06/08/2015									
		APPROVED Roger Tsai	06/08/2015									
ANGULAR ±1°												
UNLESS OTHERWISE SPECIFIED		CUST DWG	PROJECT CODE SKT						UNIT mm	SIZE A3	PART No. G878CX12T1EU	
		DWG TYPE		SCALE NA	SHEET 1 OF 2	DWG No. G878CX12T1EU		REV. A				

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.



ORIGINAL





REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
A	NE-15065	RELEASE REVISION	06/08/2015	Roger Tsai

PACKING MATERIAL



PART NAME	DIM(mm)
CARTON	580X580X210



PACKING CAPACITY

PCS/RE	RE/BC	PCS/BC
15,000PCS/RE	8 RE/BC	120,000 PCS/BC



PULL OUT DIRECTION



TOLERANCE		APPROVALS		DATE		TITLE G878 SERIES, SOCKET CRIMP TYPE CONTACT FOR 1.25 PITCH			Amphenol®			
X. X.X X.XX X.XXX	±0.30 ±0.20 ±0.10	DRAWN	Aqua Chou	06/08/2015					Amphenol Corporation			
		CHECKED	Roger Tsai	06/08/2015					Amphenol Taiwan Corporation			
		APPROVED	Roger Tsai	06/08/2015								
ANGULAR ±1°									UNIT mm	SIZE A3	PART No. G878CX12T1EU	
UNLESS OTHERWISE SPECIFIED		DWG TYPE CUST DWG		PROJECT CODE SKT					SCALE NA	SHEET 2 OF 2	DWG No. G878CX12T1EU	REV. A