




REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
B	PRODUCT DRAWING (EAR 14658)	MAY4/18	K.L.




TERMINATION-MTG. OPTION 030

.120 [3.05] DIA. THROUGH HOLES (2 PLACES), SEE ORDERING CODE.




TERMINATION-MTG. OPTION 130

VERTICAL MOUNT, #4-40 UNC THREADED THROUGH STANDOFFS




TERMINATION-MTG. OPTION 132

VERTICAL MOUNT, #4-40 UNC STANDOFFS WITH BOARDLOCKS




TERMINATION-MTG. OPTION 230

VERTICAL MOUNT, #4-40 UNC HEX JACK SOCKETS, STANDOFFS



TERMINATION-MTG. OPTION 232

VERTICAL MOUNT, #4-40 UNC HEX JACK SOCKETS, STANDOFFS WITH BOARDLOCKS



ORDERING CODE:

PART NUMBER: 1 7 E H D - 0 1 5 P X X - X 3 X

SERIES

NUMBER OF CONTACTS


STYLE
P=PIN

TERMINATION-MOUNTING OPTIONS

030=VERTICAL MOUNT, .120 [3.05] THROUGH HOLE
130=VERTICAL MOUNT, #4-40 UNC STANDOFFS
132=VERTICAL MOUNT, #4-40 UNC STANDOFFS WITH BOARDLOCKS
230=VERTICAL MOUNT, #4-40 UNC HEX JACK SOCKETS, STANDOFFS
232=VERTICAL MOUNT, #4-40 UNC HEX JACK SOCKETS, STANDOFFS WITH BOARDLOCKS

CONTACT PLATING OPTIONS

AA=ENGAGEMENT AREA 3μ" [0.08 MICRONS] GOLD FLASH
CH=ENGAGEMENT AREA 15μ" [0.38 MICRONS] GOLD
AM=ENGAGEMENT AREA 30μ" [0.76 MICRONS] GOLD



LOCATE HOLES
Φ .005 [0.13]
POSITION
DIMENSIONS ARE
BASIC

RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

SPECIFICATIONS:

MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT

SHELL: STEEL, NICKEL PLATED

INSERTS: HIGH TEMPERATURE RESISTANT NYLON, GLASS REINFORCED, UL FLAMMABILITY RATING 94V-0, COLOUR: BLACK

CONTACTS: COPPER ALLOY, GOLD PLATING (SEE ORDERING CODE) OVER 50u" [1.27 MICRONS] NICKEL ON ENGAGEMENT AREA WITH 100u" [2.54 MICRONS] MIN. MATTE TIN ON CONTACT TERMINALS.

BOARDLOCK: COPPER ALLOY, TIN PLATED

ELECTRICAL DATA:

CURRENT RATING: 3 AMP

CONTACT RESISTANCE: 15 MILLIOHMS MAX.

INSULATION RESISTANCE: 3000 MEGOHMS MIN.

DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC rms

OPERATING TEMPERATURE: -55°C TO +105°C

DRAWN	E.CHEN	DATE	JUN19/06
DESIGNED			
CHECKED	K.LAMBIE	JUL26/06	
I. E. APPRD.			
Q. A. APPRD.			
DWG. APPRD.			
ENG. REL. NO.			
REF.	EAR 12956		
DIMENSIONS ARE IN	INCHES	CODE ID. NO.	03554

Amphenol Canada Corp.

TITLE: 17EHD SERIES HIGH DENSITY D-SUB CONNECTOR, 15 SIZE PIN, VERTICAL PCB MOUNT CONTACTS, PLATING & MOUNTING OPTIONS, RoHS COMPLIANT

DWG	DRAWING NO.	REV.
C	P-17EHD-015PXX-X3X	B
SCALE	2/1	WT. -----
SURF.	-----	SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.