



Roll over image to zoom in

15m SC-ST 62.5/125 OM1 Duplex Multimode Fiber Optic Cable - Low Smoke Zero Halogen LSZH - Orange

62.5/125 micron cable for fast ethernet, fibre channel, ATM and gigabit ethernet applications where protection from toxic and corrosive gases is critical

★★★★★

0 Reviews

Product # : 36473

Connector 1 : (1) SC Male

Connector 2 : (1) ST Male

Lengths :

49.2ft

3.3ft

6.6ft

9.8ft


13.1ft

[+ show all lengths](#)

[Request availability](#)



Add



[print](#) [share](#) [chat](#)

Product Info

★ Customer Reviews

Questions & Answers

Distributors

More Choices

Description

Certifications

Specs

Product Description

With SC to ST termination, this high quality fiber optic patch cable is specifically designed for fast ethernet, fiber channel, ATM and gigabit ethernet applications. The SC connector features a push-pull locking system while the ST connector features a bayonet locking system. The LSZH jacket is composed from materials that lessen the smoke and halogen emissions when the cable is exposed to extreme temperatures.

This reduces the amount of harmful toxic and corrosive gases that cabling made with plastic materials would otherwise emit into the air during combustion. This construction makes LSZH cables ideal for use where the protection of people and equipment from harmful corrosive gases is absolutely critical. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 62.5/125 multimode fiber, immune to electrical interference.

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color :	Orange
Length :	15.00 Meter
UPC :	757120364733
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.482 LB

- Optical Multimode 1 (OM1) fiber supporting 200/500 MHz.km OFL at 850/1300 nm.
- SC Connector Dimensions: 10.6mm Height x 26mm Width x 58mm Depth (with installed duplex clip)
- ST Connector Dimensions: 9.8mm Height x 19.6mm Width x 59mm Depth
- Maximum Connector Loss: 0.50 dB
- Typical Connector Loss: 0.30 dB
- Typical Return Loss: -25 dB
- Buffer Material: PVC
- Buffer OD: 900 µm
- Jacket Material: LSZH PVC (OFNR riser-rated)
- Jacket OD: 2.8 mm
- Installation Tensile Load: 100 N (445 lbs)
- Long-Term Tensile Load: 50 N (222 lbs)
- Maximum Tensile Load: 100 N/cm
- Installation (Loaded) Minimum Bend Radius: 5.0cm (1.97in)
- Long-Term (Unloaded) Minimum Bend Radius: 3.0cm (1.2in)
- Crush Resistance: 750 N/cm
- Impact Resistance: 1,000 cycles
- Flex Resistance: 5,000 cycles
- Attenuation at 1300 nm: 1.0 dB/km
- Attenuation at 850 nm: 3.5 dB/km
- Operating Temperature: -20°C to +70°C

Please Note: Attenuation testing performed in accordance with EIA/TIA-455-171A.

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [v](#) [b](#)

