

Catalog No. TY5275M

Description: CBL TIE 120LB 18IN NATURAL NYLON

UPC No 786210870816

Home > Wire & Cable Management > Ty-Rap > Cable ties

High Performance Cable Tie, Natural Color Nylon 6.6, Length of 457mm (18 Inches) for Bundle Diameter up to 127mm (5 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F)

Representative Image

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds , 534 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.27 in , 6.9 mm
Length	18 in , 457 mm
Thickness	0.06 in , 1.5 mm
Bundle Diameter	Max 5 in , Max 127 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	6.9 mm
Band width	0.27 inch
Length belt/tape/tie	457 mm
Length belt/tape/tie	18 inch
Tie thickness	1.5 mm
Tie thickness	0.06 inch
Max. bundle diameter	127 mm
Max. bundle diameter	5 inch
Min. holding force	540 N
Operation temperature	-60-+85 °C
Operation temperature	-76-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V2