



228KXM016M

RADIAL LEAD HIGH FREQUENCY/ LOW IMPEDANCE

Parts are RoHS compliant

Date code when parts became RoHS: 23

APPLICATIONS: Switching power supplies, input filters, coupling, bypass

ELECTRICAL SPECIFICATIONS

Capacitance: 2200 uF

Dissipation Factor: 0.16 Max at 120 Hz and 20°C

Temperature Range: -55°C to +105°C

Impedance: 0.018Ohms100 kHz20°C

0.045Ohms100 kHz-10°C

Tolerance: -20 %, +20 %

WVDC: 16 Volts DC

SVDC: 20 Volts DC

Ripple Current: 2770 mA at 100 kHz and 105°C

Impedance Ratios:-25°C/20°C 2 and -40°C/20°C - 4

Leakage Current: .01CV or 3uA, whichever is greater

352 uA after 2 Minutes

Load Life: 5000 hours at 105°C with 100 % of rated voltage and with 100 % of rated ripple current

Capacitance Change: ≤20% of initial measured value

Dissipation Factor: ≤200% of maximum specified value

Leakage Current: ≤100% of maximum specified value

Frequency Multipliers:

50 HZ	120 HZ	400 HZ	1 KHZ	10 KHZ	100 KHZ
0.68	0.83	0.9	0.96	1	1

Temperature Multipliers:

45°C	60°C	70°C	65°C	75°C	85°C	105°C	125°C
2.23	2.17	2	2.1	1.75	1.75	1	0

PHYSICAL DIMENSIONS

Diameter (D): 12.5 mm + 0.5 mm

Length (L): 25 mm + 2 mm


Lead Spacing (S): 5 mm +/- 0.5 mm

Coating: BrownPET sleeving

Lead Wire Diameter (d): 0.6 mm +/- 0.05 mm

Lead Length: 15 mm +/- MIN mm

Lead Finish: Matte Tin



2400 East Devon Avenue Suite 292 Des Plaines, IL 60018 (847) 675-1760 FAX (847) 673-2850

Illinois Capacitor (HK) Ltd., Tel: 85227930931, Fax: 85227930731, www.illcap.com.hk

© Copyright 2020 Illinois Capacitor. An affiliate of Cornell Dubilier, All Rights Reserved