



Part Number : [192110002](#)
Product Description : Krimptite Wire Pin
Terminal for 12-10 AWG Wire, Mylar Tape
Carrier
Series Number : 19211
Status : Active
Product Category : Crimp Terminals
Engineering Number : WP-1210T
Packaging Alternative : 192110001 (Bag)



Documents & Resources

Drawings
[192110002_sd.pdf](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19211
Description	Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Application	Power, Wire-to-Component
Comments	Pin Length 11.43mm
Product Name	Wire Pin
UPC	800753053205

Agency

CSA	LR18689
UL	E32244

Physical

Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.465/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.45mm max.
Wire Size (AWG)	10, 12
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270088</u>
Mini-Mac Applicator	<u>638851000</u>

This document was generated on Mar 02, 2025