
Part Number : 1510641209
Product Description : 2.00mm Pitch, Milli-Grid PCB Header, Single Row, Right-Angle, Surface Mount, 0.38µm Gold (Au) Plating, without Peg, 9 Circuits, Tube
Series Number : 151064
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

1510641209_sd.pdf

PK-151062-0001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

503940001-AS-000.pdf

PS-151062-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	151064
Description	2.00mm Pitch, Milli-Grid PCB Header, Single Row, Right-Angle, Surface Mount, 0.38µm Gold (Au) Plating, without Peg, 9 Circuits, Tube
Application	Signal, Wire-to-Board
Comments	See Product Specification for maximum current rating by wire AWG
Component Type	PCB Header
Product Name	Milli-Grid
UPC	889056632454

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.5A

Downloaded from Arrow.com.

Voltage - Maximum	125V AC

Physical

Breakaway	No
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.909/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.380µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +70°C
Termination Interface Style	Surface Mount

Downloaded from Arrow.com.

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Milli-Grid Single Row Receptacle Housings	151100

Downloaded from Arrow.com.