



DO NOT SCALE		METRIC		THIRD ANGLE PROJECTION	
DIMENSIONS IN mm					
LTR	DESCRIPTION	DWN	APPD	DATE	
K1	ECO-09-025714	KK	AEG	17DEC09	



NOTES :

- FOR USE ON MINI HD APPLICATOR (LEFT - RIGHT FEED).
- TINPLATING THICKNESS .000080 MIN - .000400 MAX. (INCH).
- MATERIAL PH.BRONZE ACC ASTM B103 ALLOY 511.
-  REAR ROLLING MUST TOUCH TAB.

 **5** OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




WIRE	CRIMP HEIGHT	CRIMP WIDTH
0.5mm?	1.43mm	.080 'F'
0.75mm?	1.52mm	.080 'F'
1.0mm?	1.61mm	.080 'F'



 OBSOLETE	100015-4	PRE-TINPLATED	PH.BRONZE	216329-4
	100015-3	SILVERPLATED	PH.BRONZE	216329-3
	100015-2	TINPLATED	PH.BRONZE	216329-2
	100015-1	UNPLATED	PH.BRONZE	216329-1
	LOOSE PIECE NR.	FINISH	MATERIAL	PARTNUMBER
 OBSOLETE	CUSTOMER DRAWING		tyco Electronics	
	FOR REFERENCE ONLY WILL NOT BE UPDATED		THIS DRAWING IS UNPUBLISHED CUSTOMER DRAWING	
			© COPYRIGHT 2002 - BY AMP-SPAIN ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.	
	DR. R.v.Lokven	DATE 24.04.89	WIRE RANGE 0.5-1.0mm?	NAME .250 L.I.F AUTOMOTIVE POS LOCK REC MKII.
	CHK. R.v.Lokven	DATE 24.04.89	INSUL.RANGE 1.4-2.3 DIA	REV.DATE D M Y 17 12 09
APP. L.v.Soest		DATE 26-11-89	SIZE A2	SHEET 1 OF 1
		DWG. No.	C-216329	
				REV.LTR. K1

DIRECTION OFF TOP OF REEL



107 - 3 FIG 6.