Part Number : 2451300230
Product Description : Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Single Row, Matte Tin (Sn) Plating, 3.0m Length, 2 Circuits, Black
Series Number : 245130
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2451300230_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	245130
Description	Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Single Row, Matte Tin (Sn) Plating, 3.0m Length, 2 Circuits, Black
Application	Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Product Name	Nano-Fit
Type	Overmolded Assembly
UPC	191128813389

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Length	3.0m
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin

Downloaded from Arrow.com.

Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	98.510/g
Number of Rows	1
Overmolded	Yes
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 2464
Wire Size (AWG)	20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 2 Circuits, with Kinked Pins, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray	1053091102
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 2 Circuits, with Solder Clips, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray	1053111102
Nano-Fit Right-Angle Header, Through Hole, 2.50mm Pitch, Single Row, 2 Circuits, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray	1053131102
Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Single Row, 2 Circuits, 0.76µm Tin (Sn) Plating, with Pick-and-Place Tape, Black, Glow-Wire Capable	1054311102
Nano-Fit Right-Angle Header,	1054301102

Downloaded from Arrow.com.

Surface Mount, 2.50mm Pitch, Single Row, 2 Circuits, 0.76µm Tin (Sn) Plating, Black, Glow-Wire Capable	
Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Single Row, 2 Circuits, Black, Glow-Wire Capable	2002771102
Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Single Row, 2 Circuits, Black, Panel Mount, Glow-Wire Capable	2002771202

Downloaded from Arrow.com.