



REV.	DATE	ECR NO.	DESCRIPTION
NC	12/01/11	XXXXXX	INITIAL RELEASE



1. IMPEDANCE: 50 OHM
2. FREQUENCY RANGE: DC 0 – 11 GHz
3. DIELECTRIC WITHSTANDING VOLTAGE: 2500 VRMS, MIN.
4. DURABILITY: 500 CYCLES MIN.
5. TEMPERATURE RANGE: -65°C TO +165°C

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex								
					DRAWN M.ZHANG		12/01/11										
					CHECKED				PART DESCRIPTION N FEMALE TO FEMALE R/A ADAPTER								
					ISSUED												
SHEET 1 OF 1				PART NO. 172365													
CAD FILE C:/CONNEX/172365.DWG																	
3					CONTACT PIN	PHOSPHOR BRONZE	GOLD	1	DWG. NO. 172365.DWG					REV. NC	SIZE A	SCALE NA	
2					INSULATOR	PTFE	NATURAL	1									
1					BODY	BRASS	NEXCOTE	1									
DESCRIPTION					MATERIAL	FINISH	QTY										