



Part Number : [192890010](#)


Product Description : Die Set (Large) for the HHLS Hydraulic Crimper

Series Number : 207125

Status : Active

Product Category : Applicators and Crimp Modules

Engineering Part Number : HHL-G-740



Documents and Resources

Tooling Specifications

[ATS-192890010-001.pdf](#)

[TM-640160065-001.pdf](#)

[TM-640160065CN-001.pdf](#)

[TM-640160065DE-001.pdf](#)

[TM-640160065SP-001.pdf](#)

[TM-640160065FR-001.pdf](#)

[TM-640160065IT-001.pdf](#)

[TM-640160065JP-001.pdf](#)

[TM-640160065KR-001.pdf](#)

[TM-640160065MY-001.pdf](#)

[TM-640160065PL-001.pdf](#)

[TM-640160065RU-001.pdf](#)

[TM-640160065SK-001.pdf](#)

[TM-640160065TH-001.pdf](#)

[TM-640160065VN-001.pdf](#)

[TM-640160065TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant

Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207125
Description	Die Set (Large) for the HHLS Hydraulic Crimper
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	ETC
Tool Type	Crimp Module
UPC	800753111646
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex

	<p>and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>
--	--

Physical

Net Weight	1.000/g
------------	---------

Applicable Parts

Description	Part Number
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 1/2" (M12), Carton	<u>190670090</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Carton	<u>190670092</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/16" (M8), Carton	<u>190670093</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 7/16" (M11), Carton	<u>190670094</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 10 (M5), Carton	<u>190670095</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 1/4" (M6), Carton	<u>190670096</u>
NylaKrimp Funnel Entry Ring	<u>190670097</u>

Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Carton	
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/16" (M8), Carton	<u>190670098</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/8" (M16), Carton	<u>190670130</u>
InsulKrimp Ring Tongue Terminal for 2 AWG Wire, Carton	<u>190710272</u>
InsulKrimp Ring Tongue Terminal for 2 AWG Wire, Carton	<u>190710273</u>
InsulKrimp Ring Tongue Terminal for 2 AWG Wire, Carton	<u>190710279</u>
InsulKrimp Ring Tongue Terminal for 2 AWG Wire, Carton	<u>190710281</u>
InsulKrimp Ring Tongue Terminal for 2 AWG Wire, Carton	<u>190710283</u>
InsulKrimp Ring Tongue Terminal for 2 AWG Wire, Carton	<u>190710285</u>
InsulKrimp Butt Splice for 2 AWG Wire, Carton	<u>191540049</u>

This document was generated on Apr 14, 2026