



Part Number : [1052630002](#)

Product Description : Cellular 6 Band Antenna,
150.00mm Cable Length, Compatible with U.FL / I-PEX
MHF Connectors

Series Number : 105263

Status : Active

Product Category : Antennas



Documents and Resources

Drawings

[1052630002_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PK-105263-001-001.pdf](#)

[PS-105263-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:75e8d16b-c20f-4298-b8be-4a6708d6cb6d
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	105263
Description	Cellular 6 Band Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	Cellular 6-Band Stand Alone
Protocol	Cellular
Type	Cellular Antenna, Internal
UPC	887191106274

Electrical

Band#1 F_End (MHz)	894
Band#1 F_Start (MHz)	824
Band#2 F_End (MHz)	960
Band#2 F_Start (MHz)	880
Band#3 F_End (MHz)	1880
Band#3 F_Start (MHz)	1710
Band#4 F_End (MHz)	1990

Band#4 F_Start (MHz)	1850
Band#5 F_End (MHz)	2170
Band#5 F_Start (MHz)	1920
Band#6 F_End (MHz)	2690
Band#6 F_Start (MHz)	2500
Electrical Connectivity	Cable
Peak Gain (dBi)	2.2 @ 824 MHz, 3.0 @ 1710 MHz
Return Loss - S11 (dB)	< -6.8
Total Efficiency	> -1.7dB @ 824 MHz, > -2.2dB @ 1710 MHz

Physical

Cable Length	150.00mm
Length	106.70mm
Mounting Style	Adhesive
Net Weight	1.014/g
Packaging Type	Tray
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	13.00mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	<u>734120110</u>

This document was generated on Dec 26, 2025