




Home> Products > MICRO SWITCH™ Toggle Switches> TW> Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

12TW19-70-A002



Actual product appearance may vary.

TW Series Toggle Switch, 2 pole, 3 position, Solder terminal, Tab Lever

Features

Save space and weight
SPDT and DPDT circuitry
Temperature range: -85° F to +160° F (-65° C to +71° C)
Sealed bushing versions
Choice of 1/8 in. or 15/32 in. bushing
Color tab available on 15/32 in. bushing
UL recognized



Potential Applications

Industrial machinery and equipment
Military and commercial aviation
Construction equipment
Test instruments
Agricultural machinery
Process control
Medical instrumentation

Description

MICRO SWITCH™ miniature toggle switches in two bushing sizes. Molded in terminals are plated for soldering. Momentary and maintained circuitry closures available. Special on-on-on circuitries are also available. Pull-to-unlock levers prevent accidental operation.

Supporting Documentation

-  [Accessory: Lever Sleeve](#)
-  [Terminal Identification](#)
-  [Accessory: Seals](#)
-  [Panel Cutout](#)
-  [Accessory: Nuts](#)
-  [Engineering Drawing](#)

Product Specifications	
Circuitry/Operating action	
Product Type	MICRO SWITCH™ Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac, 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	3 position
Mounting	Bushing 15/32 in
Termination	Solder
Lever Type	Tab
UL/CSA Rating Code	L117: 5 A at 125 Vac
Comment	Black
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TW

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search