

Features:

- Small size and light weight
- Reliability and high quality
- Wider terminations provide higher power handling and more robust thermal performance
- RoHS compliant, REACH compliant, lead free, and halogen free
- AEC-Q200 compliant



Electrical Specifications - Standard

Type/Code	Power Rating (W) @ 70°C	Maximum Working Voltage (V) ⁽¹⁾	Maximum Overload Voltage (V)	TCR (ppm/°C)	Ohmic Range (Ω) and Tolerance ⁽²⁾
					1%, 5%
RMCW0508	0.75	200	400	±200 ±100	1 - 9.1 10 - 10M
RMCW0612	0.75	200	400	±200 ±100	1 - 9.1 10 - 10M
RMCW1020	1	200	400	±200 ±100	1 - 9.1 10 - 10M
RMCW1218	1	200	400	±200 ±100	1 - 9.1 10 - 10M
RMCW1225	2	200	400	±200 ±100	1 - 9.1 10 - 10M

(1) Lesser of $\sqrt{P \cdot R}$ or maximum working voltage

(2) E96 resistance values may be available in 1% tolerance but will be subject to a high MOQ's - contact Stackpole

Electrical Specifications - High Power

Type/Code	Power Rating (W) @ 70°C	Maximum Working Voltage (V) ⁽¹⁾	Maximum Overload Voltage (V)	TCR (ppm/°C)	Ohmic Range (Ω) and Tolerance ⁽²⁾
					1%, 5%
RMCW0508-HP	1	200	400	± 150 ± 100	1 - 9.1 10 - 1M
RMCW0612-HP	1.5	200	400	±100	1 - 10M
RMCW1020-HP	2	200	400	±100	1 - 10M
RMCW1218-HP	2	200	400	±100	1 - 10M
RMCW1225-HP	3	200	400	±100	1 - 10M


(1) Lesser of $\sqrt{P \cdot R}$ or maximum working voltage

(2) E96 resistance values may be available in 1% tolerance but will be subject to a high MOQ's - contact Stackpole

Electrical Specifications - Jumper

Type/Code	Jumper Rated Current (A)	Maximum Overload Current (A) < 1 second and 1 time	Jumper Resistance Value
RMCW0612	4	15	0.02 max.
RMCW1020	6	22	
RMCW1218	6	22	
RMCW1225	8	30	

Mechanical Specifications




Type/Code	L	W	H	I1	I2	Unit
RMCW0508	0.049 ± 0.004 1.25 ± 0.10	0.079 ± 0.004 2.00 ± 0.10	0.022 ± 0.004 0.55 ± 0.10	0.010 ± 0.008 0.25 ± 0.20	0.020 ± 0.008 0.50 ± 0.20	inches mm
RMCW0612	0.063 ± 0.008 1.60 ± 0.20	0.126 ± 0.008 3.20 ± 0.20	0.022 ± 0.004 0.55 ± 0.10	0.012 ± 0.008 0.30 ± 0.20	0.020 ± 0.008 0.50 ± 0.20	inches mm
RMCW1020	0.098 ± 0.008 2.50 ± 0.20	0.197 ± 0.008 5.00 ± 0.20	0.022 ± 0.004 0.55 ± 0.10	0.016 ± 0.008 0.40 ± 0.20	0.030 ± 0.008 0.75 ± 0.20	inches mm
RMCW1218	0.122 ± 0.004 3.10 ± 0.10	0.181 ± 0.004 4.60 ± 0.10	0.022 ± 0.002 0.55 ± 0.05	0.016 ± 0.008 0.40 ± 0.20	0.020 ± 0.008 0.50 ± 0.20	inches mm
RMCW1225	0.126 ± 0.008 3.20 ± 0.20	0.256 ± 0.008 6.50 ± 0.20	0.022 ± 0.008 0.55 ± 0.20	0.016 ± 0.008 0.40 ± 0.20	0.030 ± 0.008 0.75 ± 0.20	inches mm
RMCW1225-HP	0.126 ± 0.008 3.20 ± 0.20	0.256 ± 0.008 6.50 ± 0.20	0.026 ± 0.008 0.65 ± 0.20	0.016 ± 0.008 0.40 ± 0.20	0.030 ± 0.008 0.75 ± 0.20	inches mm

Performance Characteristics


Test Item	Test Method	Test Specification		Test Condition
		1%	5%	
Temperature Coefficient of Resistance	JIS-C-5201-1 4.8 IEC-60115-1 4.8	Within the specified tolerance		At 25 / -55°C and 25 / +155°C, 25°C is the reference temperature
Short Time Overload	JIS-C-5201-1 4.13 IEC-60115-1 4.13	± (1% + 0.05Ω)	± (2% + 0.1Ω)	6.25 times rated power or max. overload voltage whichever is less for 5 seconds, except for high power (-HP).
				For high power (-HP): 5 times rated power or max. overload voltage whichever is less for 5 seconds
		Jumper: max 0.02 Ω after test		Jumper: overload current for 5 seconds 0612=10 A, 1020=15 A, 1218=15 A, 1225=20 A
Leaching	JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1	Individual leaching area ≤ 5% Total leaching area ≤ 10%		260 ± 5°C for 30 seconds
Resistance to Soldering Heat	JIS-C-5201-1 4.18 IEC-60115-1 4.18	± (0.5% + 0.05Ω)	± (1% + 0.05Ω)	260 ± 5°C for 10 seconds
Rapid Change of Temperature	JIS-C-5201-1 4.19 IEC-60115-1 4.19	± (0.5% + 0.05Ω)	± (1% + 0.1Ω)	-55 to +155°C, 5 cycles
Resistance to Solvent	JIS-C-5201-1 4.29	± (0.5% + 0.05Ω)	± (0.5% + 0.05Ω)	The tested resistor should be immersed into isopropyl alcohol of 20 ~ 25°C for 60 seconds. Then the resistor is left in room temperature for 48 hours
		Jumper: max 0.02 Ω after test		
Damp Heat with Load	JIS-C-5201-1 4.24 IEC-60115-1 4.24	± (1% + 0.05Ω)	± (2% + 0.05Ω)	40 ± 2°C, 90 ~ 95% R.H. RCWV or Max. Working voltage whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF"
		Jumper: max 0.02 Ω after test		
Load Life (Endurance)	JIS-C-5201-1 4.25 IEC-60115-1 4.25.1	± (1% + 0.05Ω)	± (3% + 0.1Ω)	70 ± 2°C, RCWV or Max. Working voltage whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF"
		Jumper: max 0.02 Ω after test		
Insulation Resistance	JIS-C-5201-1 4.6 IEC-60115-1 4.6	≥ 10 GΩ		Apply 100 VDC for 1 minute
Bending Strength	JIS-C-5201-1 4.33 IEC-60115-1 4.33	± (1% + 0.05Ω)		Bending once for 5 seconds. D: 0508, 0612, 1020, 1218, 1225 = 2 mm

Operating temperature range is -55 to 155°C


Power Derating Curve:




RMCW Single Pulse and Continuous Pulse - Power x Time



RMCW and RMCS-HP Single Pulse - Voltage x Time




RMCW-HP Single Pulse and Continuous Pulse - Power x Time




The data provided is for reference only. It is typical performance for this product but it is not guaranteed. The actual pulse handling of each individual resistor may vary depending on a variety of factors including resistance tolerance and resistance value. Stackpole Electronics, Inc. assumes no liability for the use of this information. Customers should validate the performance of these products in their applications. Contact Stackpole to discuss specific pulse application requirements.

Surface Temperature x Power Rating



- 1) Resistance value used for each size was at or near critical value.
- 2) Used poor heat conduction PCB.
- 3) applied full power for 10 minutes prior to measurement.
- 4) Data for reference only. Actual performance under customer conditions may vary.


Recommended Pad Layouts




Type/Code	A	B	C	Unit
RMCW0508	0.016 0.40	0.071 1.80	0.079 2.00	inches mm
RMCW0612	0.024 0.60	0.114 2.90	0.126 3.20	inches mm
RMCW1020	0.030 0.75	0.134 3.40	0.197 5.00	inches mm
RMCW1218	0.080 2.04	0.167 4.24	0.189 4.80	inches mm
RMCW1225	0.033 0.85	0.146 3.70	0.252 6.40	inches mm

Recommended Soldering Parameters

Wave Solder Temperature Condition



Solder Reflow Temperature Condition




Rework temperature (hot air equipment) is 350°C, 3 ~ 5 seconds

Recommended reflow methods:


- IR, vapor phase oven, hot air oven
- If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

Reel Specifications




Type/Code	Reel		A	B	C	D	W	M	Unit
	Size	Quantity							
0508 and 0612	7"	5000	0.079 ± 0.020 2.00 ± 0.50	0.531 ± 0.039 13.50 ± 1.00	0.827 ± 0.039 21.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.453 ± 0.079 11.50 ± 2.00	7.008 ± 0.079 178.00 ± 2.00	inches mm
1020, 1218, 1225	7"	4000	0.079 ± 0.020 2.00 ± 0.50	0.531 ± 0.039 13.50 ± 1.00	0.827 ± 0.039 21.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.630 ± 0.079 16.00 ± 2.00	7.008 ± 0.079 178.00 ± 2.00	inches mm

Packaging Specifications - Paper Tape



Type/Code	A	B	W	E	F	Unit
RMCW0508	0.059 ± 0.006 1.50 ± 0.15	0.089 ± 0.006 2.25 ± 0.15	0.315 ± 0.008 8.00 ± 0.20	0.069 ± 0.004 1.75 ± 0.10	0.138 ± 0.002 3.50 ± 0.05	inches mm
RMCW0612	0.075 ± 0.008 1.90 ± 0.20	0.138 ± 0.008 3.50 ± 0.20	0.315 ± 0.008 8.00 ± 0.20	0.069 ± 0.004 1.75 ± 0.10	0.138 ± 0.002 3.50 ± 0.05	inches mm
Type/Code	G	H	T	D	P	Unit
RMCW0508	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.030 ± 0.004 0.75 ± 0.10	0.059 ± 0.004 / -0 1.50 ± 0.10 / -0	0.157 ± 0.004 4.00 ± 0.10	inches mm
RMCW0612	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.030 ± 0.004 0.75 ± 0.10	0.059 ± 0.004 / -0 1.50 ± 0.10 / -0	0.157 ± 0.004 4.00 ± 0.10	inches mm


Packaging Specifications - Plastic Tape



Type/Code	A	B	W	E	F	G	Unit
RMCW1020	0.110 ± 0.008 2.80 ± 0.20	0.220 ± 0.008 5.60 ± 0.20	0.472 ± 0.004 12.00 ± 0.10	0.069 ± 0.004 1.75 ± 0.10	0.217 ± 0.002 5.50 ± 0.05	0.157 ± 0.004 4.00 ± 0.10	inches mm
RMCW1225	0.134 ± 0.008 3.40 ± 0.20	0.264 ± 0.008 6.70 ± 0.20	0.472 ± 0.004 12.00 ± 0.10	0.069 ± 0.004 1.75 ± 0.10	0.217 ± 0.002 5.50 ± 0.05	0.157 ± 0.004 4.00 ± 0.10	inches mm
RMCW1225-HP	0.134 ± 0.008 3.40 ± 0.20	0.264 ± 0.008 6.70 ± 0.20	0.472 ± 0.004 12.00 ± 0.10	0.069 ± 0.004 1.75 ± 0.10	0.217 ± 0.002 5.50 ± 0.05	0.157 ± 0.004 4.00 ± 0.10	inches mm
RMCW1218	0.134 ± 0.008 3.40 ± 0.20	0.181 ± 0.008 4.60 ± 0.20	0.472 ± 0.004 12.00 ± 0.10	0.069 ± 0.004 1.75 ± 0.10	0.217 ± 0.002 5.50 ± 0.05	0.157 ± 0.004 4.00 ± 0.10	inches mm
Type/Code	H	T	D	D1	T1	P	Unit
RMCW1020	0.079 ± 0.002 2.00 ± 0.05	0.009 ± 0.004 0.23 ± 0.10	0.059 +0.004 / -0 1.50 +0.10 / -0	0.059 ± 0.004 1.50 ± 0.10	0.033 ± 0.006 0.85 ± 0.15	0.157 ± 0.004 4.00 ± 0.10	inches mm
RMCW1225	0.079 ± 0.002 2.00 ± 0.05	0.009 ± 0.004 0.23 ± 0.10	0.059 +0.004 / -0 1.50 +0.10 / -0	0.059 ± 0.004 1.50 ± 0.10	0.033 ± 0.006 0.85 ± 0.15	0.157 ± 0.004 4.00 ± 0.10	inches mm
RMCW1225-HP	0.079 ± 0.002 2.00 ± 0.05	0.009 ± 0.004 0.23 ± 0.10	0.059 +0.004 / -0 1.50 +0.10 / -0	0.059 ± 0.004 1.50 ± 0.10	0.039 ± 0.006 1.00 ± 0.15	0.157 ± 0.004 4.00 ± 0.10	inches mm
RMCW1218	0.079 ± 0.002 2.00 ± 0.05	0.009 ± 0.004 0.23 ± 0.10	0.059 +0.004 / -0 1.50 +0.10 / -0	0.059 ± 0.004 1.50 ± 0.10	0.033 ± 0.006 0.85 ± 0.15	0.157 ± 0.004 4.00 ± 0.10	inches mm

Peel Force of Top Cover Tape

Top adhesive peel off strength is 10~70 g.



Part Marking Instructions

E24 and E96 Values for 0612 -1225 (1% tolerance)

The nominal resistance is marked on the surface of the overcoating with the use of **four character markings**.

1. Values <100Ω will use "R" as the decimal holder.

10R0

10Ω

1000

100Ω

E24 Values (5% tolerance)

The nominal resistance is marked on the surface of the overcoating with the use of **three character markings**.

1. Values between 1Ω and 9.1Ω will use "R" as the decimal holder.
2. Values ≥10Ω will use no decimal holder.

1R0

1Ω

103

10KΩ

Jumper zero ohm marking code is "0"

0508 size is unmarked

RoHS Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union's directive regarding "Restrictions on Hazardous Substances" (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

RoHS Compliance Status				
Standard Product Series	Description	Package / Termination Type	Standard Series RoHS Compliant	Lead-Free Termination Composition
RMCW	Wide Termination Thick Film Chip Resistors	SMD	YES ⁽¹⁾	100% Matte Sn over Ni

Note (1): RoHS compliant by means of exemption 7c-l

"Conflict Metals" Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the "conflict region" of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.

Compliance to "REACH"

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, "The Registration, Evaluation, Authorization and Restriction of Chemicals", otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

Environmental Policy

It is the policy of Stackpole Electronics, Inc. (SEI) to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.

How to Order

R	M	C	W	0	6	1	2	J	T	1	0	R	0	-	H	P
Product Series		Size and W			Tolerance			Packaging				Resistance Value		Special		
RMCW	Wide Termination Thick Film Chip Resistor	Code	Std	-HP	Code	Tol	Value(*)	Code	Description	Size	Quantity	Four characters with the multiplier used as the decimal holder. 1 ohm = 1R00 10 ohm = 10R0 100 Kohm = 100K 10 Mohm = 10M0		Code	Description	
		0508	0.75	1	F	1%	E24	T	7" Reel Paper Tape	0508, 0612	5000			blank	Standard	
		0612	0.75	1.5	J	5%			7" Reel Plastic Tape	1020, 1218, 1225	4000			-HP	High Power	
		1020	1	2	Z	Jumper										
		1218	1	2												
		1225	2	3												

(*) E96 resistance values may be available in 1% tolerance and will be subject to higher MOQ's. Contact Stackpole.