



Part Number : [1717221002](#)

Product Description : zQuad Small Form Factor Pluggable Plus (zQSFP+) Stacked Integrated 2-by-1 Connector and Cage with Metal EMI Gasket, 76 Circuit, Gold (Au) Over Nickel Plated, Up/Down Light Pipe Indicators

Series Number : 171722

Status : Active

Product Category : High-Speed I/O Connectors

Documents and Resources

Drawings

[1717221002_sd.pdf](#)

[PK-171565-0001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-171722-1000-001.zip](#)

[EE-171081-3000-001.pdf](#)

[SP-171081-3000-001.zip](#)

Specifications

[AS-171565-0001-001.pdf](#)


[AS-171565-0002-001.pdf](#)

[PS-171565-0001-001.pdf](#)

[TS-171565-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Perfluorobutane sulfonic acid (PFBS) and its salts per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Connectors
Series	171722
Description	zQuad Small Form Factor Pluggable Plus (zQSFP+) Stacked Integrated 2-by-1 Connector and Cage with Metal EMI Gasket, 76 Circuit, Gold (Au) Over Nickel Plated, Up/Down Light Pipe Indicators
Application	Board-to-Board, Module-to-Board, Wire-to-Board
Component Type	Receptacle
Product Name	zQSFP Plus,zQSFP+
Type	Pluggable

UPC	887191235875
-----	--------------

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Data Rate	28.0 Gbps
Grounding to Panel	Yes
Shield Type	EMI Fingers
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	76
Circuits (maximum)	76
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	34.608/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	N/A
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	1.20mm
Pitch - Mating Interface	0.80mm
Plating min - Mating	0.762µm

Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
QSFP Cable Assemblies	<u>74757</u>

Application Tooling

This document was generated on May 14, 2026