

BWLD003025225R8J00

Search by : [Part Number](#) [Characteristics](#) [Cross reference](#)



MP ?

Wire Wound-Low DCR

- Series Pdf
- RoHSREACHCoC
- ICP Report

Product detail	
Structure	Wire Wound
L(mm) ±	2.99Max.
W(mm) ±	2.5Max.
T(mm) ±	2.2Max.
Size Code (JIS/EIA)	2520/1008
Inductance(uH)	5.8
Unit	uH
Tolerance(±%)	5
Test Frequency(L)	2.5MHz
Q Typ	21
Test Frequency(Q)	2.5MHz
SRF(MHz)Min	37
RDC(Ω)Max	0.28

Irms(mA)Max

750

Operating Temperature

- 25℃~105℃(Including self - temperature rise)

Part Numbering


Dimensions

Packing

Recommended Pattern

Electrical Characteristics

S Parameter



Products

- Power Inductor
- EMI-Common Mode Choke
- EMI-Bead
- RF-Signal Inductor
- RF-Passives/Antennas
- LAN Transformer
- Resistor & Current Sensor

Applications

- Automotive
- Industrial
- Server/DataCenter
- Communication
- Mobile and Tablet
- Computer/Laptop
- Consumer

Design Tools

- Simulation Tool
- Product Search Engine
- E-Catalogue

About Us

- Corporate Overview
- Corporate Milestones
- Core Technology

Investor

Financial Information

Corporate governance

Stakeholder Contacts

News

Media Center

New Products

Events

Product Notices

Contact Us

Contact Info

Contact Form

Join Chilisin

Terms of Use

Privacy policy

Sitemap



Inductor



Resistor



Powder

Copyrights © 2018. Chilisin. All rights reserved.