

**Microchip****Filter specification****TFS2062A****1/5****Measurement condition**

|                        |    |     |
|------------------------|----|-----|
| Ambient temperature:   | 23 | °C  |
| Input power level:     | 0  | dBm |
| Terminating impedance: |    |     |
| Input:                 | 50 | Ω   |
| Output:                | 50 | Ω   |

**Characteristics**

## Remark:

The maximum attenuation in the pass band is defined as the insertion loss  $a_e$ . The nominal frequency  $f_N$  is fixed at 2062.5 MHz without any tolerance or limit. The values of absolute attenuation  $a_{abs}$  are guaranteed for the whole operating temperature range. The frequency shift of the filter in the operating temperature range is included in the production tolerance scheme.

| D a t a                              |     |     |      |     | typ. value        |     | tolerance / limit |                    |        |      |     |
|--------------------------------------|-----|-----|------|-----|-------------------|-----|-------------------|--------------------|--------|------|-----|
| Insertion loss in PB                 |     |     |      |     | a <sub>e</sub>    | 3.3 | dB                | max.               | 4.0    | dB   |     |
| Nominal frequency                    |     |     |      |     | f <sub>N</sub>    |     |                   |                    | 2062.5 | MHz  |     |
| Passband                             |     |     |      |     | PB                |     |                   | f <sub>N</sub>     | ±      | 37.5 | MHz |
| Pass band variation                  |     |     |      |     |                   | 0.7 | dB                |                    |        | 2.0  | dB  |
| Absolute attenuation                 |     |     |      |     | a <sub>abs</sub>  |     |                   |                    |        |      |     |
| 1730                                 | MHz | ... | 1790 | MHz |                   | 42  | dB                | min.               | 38     | dB   |     |
| 1880                                 | MHz | ... | 1924 | MHz |                   | 33  | dB                | min.               | 30     | dB   |     |
| 2320                                 | MHz | ... | 2380 | MHz |                   | 50  | dB                | min.               | 40     | dB   |     |
| Return loss within passband          |     |     |      |     |                   | 14  | dB                | min.               | 10     | dB   |     |
| Input power level                    |     |     |      |     |                   |     |                   | max.               | 0      | dBm  |     |
| Operating temperature range          |     |     |      |     | OTR               |     |                   | - 45 °C ... + 85°C |        |      |     |
| Storage temperature range            |     |     |      |     |                   |     |                   | - 40 °C ... + 85°C |        |      |     |
| Temperature coefficient of frequency |     |     |      |     | TC <sub>f</sub> * | -73 | ppm/K             |                    |        |      |     |

\*)  $\Delta f(\text{Hz}) = TC_f(\text{ppm/K}) \times (T - T_0) \times f_{T0}(\text{MHz})$

**Generated:**

---



**Checked / Approved:**

---

**Microchip Frequency Technology GmbH**  
**Potsdamer Straße 18**  
**D 14 513 TELTOW / Germany**  
**Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**


Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

## Filter characteristic




## Construction and pin connection

(All dimensions in mm)



|   |        |
|---|--------|
| 1 | Ground |
| 2 | Input  |
| 3 | Ground |
| 4 | Ground |
| 5 | Output |
| 6 | Ground |

Date code: Year + week  
D 2013  
E 2014  
F 2015  
...

50  $\Omega$  Test circuit

Microchip Frequency Technology GmbH

Potsdamer Straße 18

D 14 513 TELTOW / Germany

Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

**Stability characteristics, reliability**

After the following tests the filter shall meet the whole specification:

1. Shock: 500g, 1 ms, half sine wave, 3 shocks each plane;  
DIN IEC 68 T2 - 27
2. Vibration: 10 Hz to 500 Hz, 0,35 mm or 5 g respectively, 1 octave per min, 10 cycles per plane, 3 planes;  
DIN IEC 68 T2 - 6
3. Change of temperature: -55 °C to 125°C / 15 min. each / 100 cycles  
DIN IEC 68 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: three times max.;  
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;

This filter is RoHS compliant (2011/65/EU)


**Packing**

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;  
tape type II, embossed carrier tape with top cover tape on the upper side;


|   |             |
|---|-------------|
| max. pieces of filters per reel:                    | 3000        |
| reel of empty components at start:                  | min. 300 mm |
| reel of empty components at start including leader: | min. 500 mm |
| trailer:  | min. 300 mm |

**Tape (all dimensions in mm)**

|         |                |
|---------|----------------|
| W       | : 8,00 ± 0,3   |
| Po      | : 4,00 ± 0,1   |
| Do      | : 1,50 +0,1/-0 |
| E       | : 1,75 ± 0,1   |
| F       | : 3,50 ± 0,05  |
| G(min)  | : 0,75         |
| P2      | : 2,00 ± 0,05  |
| P1      | : 4,00 ± 0,1   |
| D1(min) | : 1,50         |
| Ao      | : 3,25 ± 0,1   |
| Bo      | : 3,25 ± 0,1   |
| Ct      | : 5,3 ± 0,1    |

**Reel (all dimensions in mm)**

|         |               |
|---------|---------------|
| A       | : 180         |
| W1      | : 8,4 +1,5/-0 |
| W2(max) | : 14,4        |
| N(min)  | : 60          |
| C       | : 13,0 ± 0,2  |



The minimum bending radius is 45 mm.

**Microchip Frequency Technology GmbH**

**Potsdamer Straße 18**


**D 14 513 TELTOW / Germany**

**Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

**Air reflow temperature conditions**

| <b>Conditions</b>                          | <b>Exposure</b>             |
|--|-----------------------------|
| Average ramp-up rate (30°C to 217°C)       | less than 3°C/second        |
| > 100°C                                    | between 300 and 600 seconds |
| > 150°C                                    | between 240 and 500 seconds |
| > 217°C                                    | between 30 and 150 seconds  |
| Peak temperature                           | max. 260°C                  |
| Time within 5°C of actual peak temperature | between 10 and 30 seconds   |
| Cool-down rate (Peak to 50°C)              | less than 6°C/second        |
| Time from 30°C to Peak temperature         | no greater than 300 seconds |

**Chip-mount air reflow profile****Microchip Frequency Technology GmbH****Potsdamer Straße 18****D 14 513 TELTOW / Germany****Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

**Microchip****Filter specification****TFS2062A****5/5****History**

| <b>Version</b> | <b>Reason of Changes</b>                | <b>Name</b>   | <b>Date</b> |
|----------------|---|---------------|-------------|
| 1.0            | Generation of development specification | S.Springfeldt | 08.11.2013  |

**Microchip Frequency Technology GmbH**  
**Potsdamer Straße 18**  
**D 14 513 TELTOW / Germany**  
**Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.