

**RoHS Compliant
Pb - Lead Free
AEC-Q200 Qualified**

Ltr	Revisions	Date	Appr

Electrical Specifications:

Frequency Range	6.000 to 133.000	MHz
Mode of Oscillation	Fundamental	6.000 to 50.000
	Third Overtone	40.000 to 133.000
Frequency Tolerance at 25°C	±50	PPM Max
Frequency Stability over Temperature Range	±100	
Operating Temperature Range	-40 to +125	° C
Storage Temperature Range	-55 to +125	
Aging	±3	PPM Max/Year
Load Capacitance	10 to 32 and Series Resonance	pF
Shunt Capacitance	7.0	
Equivalent Series Resistance (ESR)	See ESR Table	Ohms
Drive Level	100	uW Typ
Insulation Resistance	500 at at 100 Vdc ± 15 Vdc	M Ohms

Frequency Range and ESR Values:

Frequency Range in MHz	ESR Ohm Max	Mode of Operation	Frequency Range in MHz	ESR Ohm Max	Mode of Operation
6.000 to 7.999	70	Fundamental	40.000 to 79.999	70	3rd Overtone
8.000 to 9.999	70	Fundamental	80.000 to 133.000	60	3rd Overtone
10.000 to 14.999	50	Fundamental			
15.000 to 39.999	30	Fundamental			
40.000 to 50.000	25	Fundamental			



11-3 Chien-Kuo Rd T.E.P.Z. 4027 Taiwan, ROC

All dimensions are millimeters.

CAD: TCR

Review: EG

Appr: JL


Page: 1/4 Date: Dec 18, 2018

Specification Title:

**Microprocessor Crystal Unit
Automotive Temperature Range
5 x 7 millimeter Surface Mount - 4 Pad
General Product Specification**


Part Number: **C7S X1 Series**

Mechanical Outline:




Package is Seam Sealed Ceramic-Metal.
Dimensions are millimeters.

Carrier Tape Dimensions:



Solder Reflow Characteristics:



How to build a Part Number:

Series		C	Parameter
Package		7S	5.0 x 7.0 mm
		-	
Frequency		6.000 to 133.000	MHz
		-	
Load Capacitance	8	8 pF	
	10	10 pF	
	12	12 pF	
	16	16 pF	
	18	18 pF	
	20	20 pF	
	32	32 pF	
	S	Series	
	-		
Frequency Tolerance	Standard	50	±50 PPM
Frequency Stability	Standard	100	±100 PPM
		-	
Mode of Oscillation	See Notes	Fundamental	
	3	Third Overtone	
	-		
Temperature Range	Standard	X1	-40 to +125 °C
		-	
Packaging	M	250pcs Reel	
	R	1000pcs Reel	

Part Number Example:

C7S-64.000-18-50100-3-X1-R

C7S- 5 x 7 mm SMD Seam Seal Package - 4 pad

64.000 MHz Nominal Frequency

18 pF Load Capacitance

50100: ±50 PPM Frequency Tolerance and ±100 PPM Frequency Stability

Third Overtone Mode

X1: -40 to +125° C Automotive Temperature Range

R: Tape and Reel Packaging 1000pcs Reel

Notes:

- 1- Fundamental mode does not need to be included in Part Number description.
- 2- Other Load Capacitances are available other than those listed in Part Number table above.
- 3- Product is shipped in Tape and Reel configuration.
- 4- Quantities less than 250pcs are shipped in tape
- 5- Specification subject to change without notice

Page:	4/4	Date:	Dec 18, 2018	P/N:	C7S X1 Series	
-------	-----	-------	--------------	------	---------------	--