


This document was generated on 05/09/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0987801518](#)
Status: **Active - Custom**
Description: 2.54mm (.100") Pitch, Male Header, PA 4.6, 6 Circuits, Dual Row, Black

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-98787-001 \(PDF\)](#)



General
Product Family Crimp Housings
Series 98780
Application Power, Wire-to-Wire
Product Name N/A

Physical
Circuits (maximum) 6
Gender Female
Glow-Wire Compliant No
Lock to Mating Part Yes
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm (.100")
Pitch - Termination Interface 2.54mm (.100")
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -40°C to +80°C

Solder Process Data
Duration at Max. Process Temperature (seconds) 40
Lead-free Process Capability SMC & Wave Capable (TH only)
Max. Cycles at Max. Process Temperature 1
Process Temperature max. C 245

Material Info
Old Part Number 18918EV6F8

Reference - Drawing Numbers
Application Specification AS-98787-001
Sales Drawing SD-98787-001

EU RoHS **China RoHS**

RoHS Compliance
Not Required

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[98780Series](#)

Mates With
[987861011 MOX Receptacle Housing](#)

This document was generated on 05/09/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION